

# Voltage tester

Model testo 750-3



### Application:

Ideally suited for testing electrical systems and devices for voltage or absence of voltage. Thanks to the LED all-round display and unique fibre-optic light guide technology, the voltage indication is clearly and distinctly visible from any position.

### Execution:

- Clear, patented LED all-round display
- Large fibre-optic light guide for optimal voltage indication
- Robust housing with ergonomic handle and anti-slip ring
- Additionally suitable for single-pole voltage testing for rapid determination of live conductors
- Additionally suitable as a continuity tester and for rotary field measurements
- Includes RCCB tripping function for testing fault current circuit breakers
- Includes vibrating load keys to avert the accidental execution of trigger tests
- Built-in pocket torch for illuminating measuring points in darkness
- LCD display for current measurement display

### Delivery:

Voltage tester incl. 2x batteries AAA, test tip protection, measuring tip attachments, calibration log and operating instructions



Art. no.	75017 210
Brand	TESTO
Manufacturer Part Number	0590 7503
Model	testo 750-3
Display	LCD
Max. continuity test	500 kOhm
Min./max. voltage range AC	12-690 V/AC
Min./max. voltage range DC	12-690 V/DC
Min./max. frequency	50 / 60 Hz
Phase-sequence test	Yes
Phase sequence test	Yes
IP protection class	IP 64
Length x width x height	270 x 70 x 35 mm
Weight	295 g
Overvoltage protection category	CAT III/1000 V, CAT IV/600 V
Min./max. working temperature	-10 to 50 °C
Gross Weight	0.355 kg
Product Group	4CF

### EAN

4029547013911

