

Air compressor MEGA 400-50 W

metabo®

Version:

- For single-phase alternating current
- Oil-lubricated piston compressor
- Belt drive for low motor speeds and quiet running
- Instrument panel with easily legible manometers for tank and operating pressure
- Cord wrap facility
- Rubberised, robust wheels and handle for mobile applications
- Steering rollers with parking brake for good manoeuvrability
- Filter pressure reducer including manometer and mist lubricator for improved air quality and controllable working pressure

Advantage:

- Push button with starter valve for reliable cold start
- 10-year tank warranty against rust penetration



Art. no.	75290 027
Model	Mega 400-50 W
Operating pressure	10 bar
Intake air capacity	400 l/min
Delivery quantity effective at 80% max. pressure	260 l/min
Filling capacity	300 l/min
Tank capacity	50 l
Power input	2200 W
Max. rotation speed	1050 rpm
Sound-pressure level	86 dB
Length x width x height	1050 x 410 x 817 mm
Weight	73 kg
With overload protection	Yes

EAN-Code

400743024445 1