

Balancer with load capacity of 3.0-21.0 kg, with automatic lock

Type 7231, cable extraction 2000 mm

AUTOSTAT

Application:

Can be used for following tools and devices, e. g.: compressed air devices, electrical devices, paint spray guns, cable-binding pliers, nailing devices, flue gas swivelling arms, robot power supply line, welding pliers, packaging devices, etc.

Execution:

- Housing made of extremely shock-resistant special plastic
- suspension via a freely turning and swivelling safety hook
- Infinitely adjustable load, via adjusting screw
- The load is attached via a safe screw snap hook
- Cable feed limitation is impact absorbing and adjustable
- Rope is infinitely variable in its length via a rope clamp
- If required, the cable can be replaced very easily
- Safety device: Protection against falling in line with DIN 15112 included in scope of delivery, spring safety device, riveted special motive spring, cable drum, can be blocked (with integrated locking device), push clamp for securing the cable end
- Working area: Cable extraction: 2000 mm, ropes in special lengths available on request
- Automatic stop allows the device to be locked. Locking not to be used for load change!

Advantage:

- Effortless work



Art. no.	77004 604
Brand	AUTOSTAT
Manufacturer Part Number	77004604
Min. load-carrying capacity	4.5 kg
Max. load-carrying capacity	7 kg
Type	7231
With automatic locking	Yes
Max. cable pull-out length	2000 mm
Adjustable cord length	Yes
Material of cord	Steel
Wire cable diameter	3 mm
Replaceable cord	Yes
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Highly abrasion-proof plastic
Suspension type	Freely rotating and pivot safety hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing width	180 mm
Housing thickness	130 mm
Colour of housing	Black
Design	Standard
Height	520 mm
Spring design	Special mainspring
With overrotation protection	No
Spring breakage protection	Yes
Number of springs	1 PCS
Gross Weight	3.600 kg
Product Group	787

EAN

4053625617265

