



ELECTRONICS, INC.  
44 FARRAND STREET  
BLOOMFIELD, NJ 07003  
(973) 748-5089  
<http://www.nteinc.com>

## **NTE74LS367** **Integrated Circuit** **TTL – Hex Bus Driver with 3-State Outputs**

### **Description:**

The NTE74LS367 is a hex bus driver in a 16-Lead plastic DIP type package designed specifically to improve both the performance and density of three-state memory address drivers, clock drivers, and bus oriented receivers and transmitters. The designer has a choice of selected combinations of inverting and non-inverting outputs, symmetrical  $\bar{G}$  (active-low control) inputs.

This device features high fan-out, improved fan-in, and can be used to drive terminated lines down to 133 ohms.

### **Features:**

- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- Non-Inverting Outputs

### **Absolute Maximum Ratings:** (Note 1)

Supply Voltage, $V_{CC}$ .....	7V
DC Input Voltage, $V_{IN}$ .....	7V
Voltage Applied to Disable 3-State Output .....	5.5V
Operating Temperature Range, $T_A$ .....	0°C to +70°C
Storage Temperature Range, $T_{stg}$ .....	-65°C to +150°C

Note 1. Unless otherwise specified, all voltages are referenced to GND.

### **Recommended Operating Conditions:**

Parameter	Symbol	Min	Typ	Max	Unit
Supply Voltage	$V_{CC}$	4.75	5.0	5.25	V
High-Level Input Voltage	$V_{IH}$	2	–	–	V
Low-Level Input Voltage	$V_{IL}$	–	–	0.8	V
High-Level Output Current	$I_{OH}$	–	–	-2.6	mA
Low-Level Output Current	$I_{OL}$	–	–	24	mA
Operating Temperature Range	$T_A$	0	–	+70	°C

### **Electrical Characteristics: (Note 2, Note 3)**

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
Input Clamp Voltage	V <sub>IK</sub>	V <sub>CC</sub> = MIN, I <sub>I</sub> = -18mA		-	-	-1.5	V
High Level Output Voltage	V <sub>OH</sub>	V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2V, V <sub>IL</sub> = MAX, I <sub>OH</sub> = MAX		2.4	3.1		V
Low Level Output Voltage	V <sub>OL</sub>	V <sub>CC</sub> = MIN, V <sub>IH</sub> = 2V, V <sub>IL</sub> = MAX		I <sub>OL</sub> = 12mA	-	0.25	0.4
				I <sub>OL</sub> = 24mA	-	0.35	0.5
Off-State Output Current	I <sub>OZ</sub>	V <sub>CC</sub> = MAX, V <sub>IH</sub> = 2V		V <sub>O</sub> = 2.4V	-	-	20 μA
				V <sub>O</sub> = 0.4V	-	-	-20 μA
Input Current	I <sub>I</sub>	V <sub>CC</sub> = MAX, V <sub>I</sub> = 7V		-	-	0.1	mA
High Level Input Current	I <sub>IH</sub>	V <sub>CC</sub> = MAX, V <sub>I</sub> = 2.7V		-	-	20	μA
Low Level Input Current A Inputs	I <sub>IL</sub>	V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.5V, Either $\overline{G}$ Input at 2V		-	-	-20	μA
		V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.4V, Both $\overline{G}$ Input at 0.4V		-	-	-0.4	mA
		V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.4V		-	-	-0.2	mA
Short-Circuit Output Current	I <sub>OS</sub>	V <sub>CC</sub> = MAX, Note 4		-40	-	-225	mA
Supply Current	I <sub>CC</sub>	V <sub>CC</sub> = MAX, Data Outputs = 0V, Output Controls = 4.5V		-	14	24	mA

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under "Recommended Operation Conditions".

Note 3. All typical values are at V<sub>CC</sub> = 5V, T<sub>A</sub> = +25°C.

Note 4. Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second.

### **Switching Characteristics: (V<sub>CC</sub> = 5V, T<sub>A</sub> = +25°C unless otherwise specified)**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Propagation Delay Time (From Any Input to Y Output)	t <sub>PLH</sub>	R <sub>L</sub> = 667Ω, C <sub>L</sub> = 45pF	-	10	16	ns
	t <sub>PHL</sub>		-	9	22	ns
Output Enable Time (From Any Input to Y Output)	t <sub>PZH</sub>	R <sub>L</sub> = 667Ω, C <sub>L</sub> = 5pF	-	19	35	ns
	t <sub>PZL</sub>		-	24	40	ns
Output Disable Time (From Any Input to Y Output)	t <sub>PHZ</sub>	R <sub>L</sub> = 667Ω, C <sub>L</sub> = 5pF	-	-	30	ns
	t <sub>PLZ</sub>		-	-	35	ns

### Pin Connection Diagram

