

PRODUCT-DETAILS

S801S-C16

S801S-C16 High Performance MCB



General Information

Extended Product Type	S801S-C16
Product ID	2CCS861001R0164
EAN	7612271200503
Catalog Description	S801S-C16 High Performance MCB
Long Description	<p>The S801S-C16 is a 1-pole High Performance Circuit breaker with C-characteristic, with cage terminal and a rated current of 16 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S801S-C16 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S801S-C16 more comfortable. Due to the fast arc extinction of S801S-C16 your application will be secured.</p>

Technical

Standards	IEC/EN 60947-2 IEC/EN 60898-1 UL 1077
Product Name	High Performance MCB
Tripping Characteristic	C
Type of Residual Current	standard version
Rated Voltage (U _r)	230 / 400 V
Rated Operational Voltage	400/690 V AC 125 V DC acc. to IEC 60898-1 400 V

Operational Voltage	Maximum 230/400 V AC Minimum 12 V AC
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 690 V
Rated Impulse Withstand Voltage (U _{imp})	8 kV
Input Voltage Type	AC
Rated Current (I _n)	16 A
Rated Operational Current (I _e)	16 A
Rated Short-Circuit Capacity (I _{cn})	(400 V) 25 kA (230 V) 25 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu})	(240 / 415 V AC) 50 kA (254 / 440 V AC) 30 kA (400 / 690 V AC) 6 kA (125 V DC) 30 kA (230 V) 50 kA
Rated Conditional Short-Circuit Current (I _{nc})	(230 V) 50 kA (400 V) 50 kA
Rated Service Short-Circuit Breaking Capacity (I _{cs})	(240 / 415 V AC) 40 kA (254 / 440 V AC) 22.5 kA (400 / 690 V AC) 4 kA (125 V DC) 30 kA
Frequency (f)	50 ... 60 Hz
Rated Frequency (f)	50...60 Hz
Power Loss	3.1 W at Rated Operating Conditions per Pole 3.1 W
Contact Position Indication	ON / OFF / TRIP
Energy Limiting Class	3
Electrical Endurance	10000 cycle 10000 cycle
Number of Poles	1
Number of Protected Poles	1
Overvoltage Category	IV
Tightening Torque	3.5 N·m 31 in·lb
Release Type	C
Actuator Marking	I / O
Housing Material	Insulation group I, RAL 7035
Mounting on DIN Rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any
Recommended Screw Driver	Pozidriv 2
Accessories Available	Yes
Remarks	Connection from top and bottom Connecting with CU only IP40 in enclosure with cover Cage terminal with captive screw
Connecting Capacity	Rigid 0 ... 50 mm ² Flexible 0 ... 70 mm ²
Terminal Type	Screw Terminals

Environmental

Ambient Temperature	-25...60 °C
Ambient Air Temperature	Operation -25...60 °C
Reference Ambient Air Temperature	acc. to IEC60947-2 30 °C acc. to EN60898-1 30 °C
Degree of Protection	IP20

Pollution Degree	3
Environmental Conditions	Damp Heat Cyclic acc. to IEC 60068-2-30 12+12 cycle Damp Heat Cyclic acc. to IEC 60068-2-30 55°C @ 90-96% Damp Heat Cyclic acc. to IEC 60068-2-30 25°C @ 90-100% Dry Heat Test B acc. to IEC 60068-2-2 16 hour @ 55 °C Dry Heat Test B acc. to IEC 60068-2-2 2 hour @ 70 °C
Resistance to Vibrations acc. to IEC 60068-2-6	2 - 13.2 Hz / 1mm 13.2 - 100Hz / 0.7g with load 100% x 1e
RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	2CCY413207D0203

Technical UL/CSA

Interrupting Rating acc. to UL1077	(240 V AC) 30 kA (277 V AC) 14 kA (347 V AC) 6 kA
------------------------------------	---

Dimensions

Width in Number of Modular Spacings	1
Product Net Width	27 mm
Product Net Height	95 mm
Product Net Depth / Length	82.5 mm
Product Net Weight	245 g
Product Net Length	27 mm
Size	1 module
Built-In Depth (t ₂)	82.5 mm

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	105 mm
Package Level 1 Height	99 mm
Package Level 1 Depth / Length	33 mm
Package Level 1 Gross Weight	270 g
Package Level 1 EAN	7612271200503

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010
E-Number (Finland)	3212102
E-Number (Switzerland)	807119315
Country of Origin	Switzerland (CH)
Selling Unit of Measure	piece

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CCC005083D0202
Environmental Information	2CCY413207D0203
Instructions and	2CCC413016M0008

Manuals

RoHS Information	2CCC005083D0202, 9AKK107680A3903
------------------	----------------------------------

Popular Downloads

Data Sheet, Technical Information	2CCC413003C0208
Instructions and Manuals	2CCC413016M0008
Dimension Diagram	2CCC413003C0201

Classifications

ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
ETIM 8	EC000042 - Miniature circuit breaker (MCB)
EPLAN Catalog Tree	Electrical engineering / Protection devices / General
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85362020
Object Classification Code	F

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → High Performance Circuit Breakers HPCBs

