



## RSF30 Series

The RSF30 series is a range of high power side entry, internally mounted devices. Mounting of this series requires access to the inside of the tank. They are manufactured in Nylon or Polypropylene, with a choice of gasket materials, to suit most commonly used liquids. The switch action may be reversed by rotating the device through 180°C.

TECHNICAL SPECIFICATIONS			ELECTRICAL SPECIFICATIONS	
Material	Nylon	Polypropylene	Switching Voltage VA	100
Colour	Black	Opaque	Switching Voltage AC	240
Temp. Range	°C	-20 / +75	Switching Voltage DC	120
	°F	-4 / +167	Switching Current Max. A	5
Min. Fluid S.G.	0.85	0.85	Breakdown Voltage DC	575
Must Close Level (S.G.=1)	20mm	23mm	All ratings are for resistive load only.	
Must Open Level (S.G.=1)	47mm	52mm		

Cynergy3	Material	Leadouts	Gaskets	Thread size
RSF33W100RC	Nylon	1m PVC 16/0.2 UL approved	Nitrile	M12x1.75
RSF34W100RF	Polypropylene	1m PVC 16/0.2 UL approved	Nitrile	M16x2



- ▶ 100W contacts available
- ▶ Rugged design
- ▶ Reliable reed switch contacts
- ▶ WRAS approval
- ▶ Many variants are UL recognised components  
File number E171218

Every effort has been made to ensure that the descriptions and specifications quoted are correct, however, no liability can be accepted for any errors or omissions in this data. The detail specifications are subject to change without prior notice.

Cynergy3 Components Ltd  
7 Cobham Road  
Ferndown Industrial Estate  
Wimborne  
Dorset BH21 7PE  
Tel: +44 (0) 1202 897969  
Fax: +44 (0) 1202 891918  
sales@cynergy3.com  
www.cynergy3.com