


MK502A



T-slot cylinder sensor

MKT2020-NI--/A/6,0M/-H/1G/1D



- 1 fastening clamp
2 Sensing face



Product characteristics

Electrical design	NAMUR
Output function	normally open
Dimensions [mm]	25 x 5 x 6.5

Electrical data

Connection to switching amplifiers	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2
Current consumption [mA]	target not detected: ≤ 1 ; target detected: $\geq 2,2$
Protection class	III

Outputs

Electrical design	NAMUR
Output function	normally open
Switching frequency DC [Hz]	2000

Detection zone

Response sensitivity [mT]	2
Travel speed [m/s]	> 10

Accuracy / deviations

Hysteresis [mm]	1
Repeatability [mm]	< 0.2

Operating conditions

Ambient temperature [°C]	-25...70
Protection	IP 65; IP 67

MK502A



T-slot cylinder sensor

MKT2020-NI--/A/6,0M/-H/1G/1D

Tests / approvals		
Approval	BVS 09 ATEX E164; IECEx BVS 09.0065	
ATEX marking	Ex II 1G Ex ia IIC T4 Ga	
	Ex II 1D Ex ia IIIC T135°C Da	
EMC	EN 61000-4-2 ESD	- kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
	EN 55011 emission	class B
MTTF [years]	2142	
Safety classification		
Max. internal capacitance [nF]	140	
Max. internal inductance [μ H]	400	
Mechanical data		
Weight [g]	93.9	
Mounting	flush mountable	
Type of mounting	fastening clamp with combined slot / hexagon socket, width across flats 1.5	
Cylinder type	T-slot cylinders	
Dimensions [mm]	25 x 5 x 6.5	
Materials	housing: PA; fastening clamp: stainless steel	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)	rubber placeholder: 1	Cable clip: 1
Remarks		
Pack quantity	1 pcs.	

MK502A




T-slot cylinder sensor

MKT2020-NI--/A/6,0M/-H/1G/1D

Electrical connection

Cable: 6 m, PVC; 2 x 0.14 mm²

Connection



Core colours :

BN = brown
BU = blue