



65MM TERMINAL MODULE FOR ET200S HIGH FEATURE LINE STARTER/LINE DIR.STARTER-STARTER WITH SUPPLY CONNECTOR

General technical data:		
<b>Product designation</b>		Terminal module
<b>Product type designation</b>		TM-DS65-S32-01 FS L
<b>Design of the product</b>		for DS1e-x and DSS1e-x, with energy bus infeed, with caps
<b>Mounting height</b>	mm	290
<b>Installation width</b>	mm	65
<b>Installation depth</b>	mm	100
<b>Protection class IP</b>		IP20
<b>Insulation voltage Rated value</b>	V	690
<b>Operating voltage</b>		
• with AC Rated value	V	500
<b>Surge voltage resistance Rated value</b>	V	6 000
<b>Operating current Rated value</b>	A	50
<b>Operating frequency</b>		
• 1 Rated value	Hz	50
• 2 Rated value	Hz	60
<b>Type of connectable conductor cross-section</b>		
• solid		1x 10 mm <sup>2</sup> , 2x (1 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 6 mm <sup>2</sup> )
• finely stranded with core end processing		2x (1 ... 2.5 mm <sup>2</sup> ), 2x (2.5 ... 6 mm <sup>2</sup> ), acc. to IEC 60947
• for AWG conductors		
— solid		2x (14 ... 10)
— stranded		2x (14 ... 10)

Installation/ mounting/ dimensions:

Size of the screwdriver tip		Standard screwdriver Size 2
Tightening torque with screw-type terminals	N·m	2 ... 2.5

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK19030AK00>


**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RK19030AK00/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RK19030AK00&lang=en>





last modified:

15.01.2015