

## DCKN insert holder, negative right

For facing with CN indexable insert



### Application:

For facing and longitudinal turning with CN indexable insert, 80°

### Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type C, pitch angle 75°, tip angle 80°, clearance angle 0°

### Advantage:

- Universal application for facing and longitudinal turning with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

<b>Art. no.</b>	<b>17684 058</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	5697857
<b>ISO name</b>	DCKN R/L 2525 M12
<b>Knife edge length</b>	12 mm
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Programming size</b>	32 mm
<b>Suitable for indexable inserts</b>	DC.. 11T3..
<b>Tool design</b>	Right
<b>Length of head</b>	32 mm
<b>Gross Weight</b>	0.752 kg
<b>Product Group</b>	1XG

### EAN

4050841508292