

## RefLED Superia Retro ES50

RefLED Superia Retro ES50 V3 230LM 827 36 SL

0029101



### Product features

- Premium performance professional LED GU10 range with the same look and feel of traditional halogen GU10 lamp
- Recreates backlight effect similar to halogen dichroic lamps
- Full glass design - means no colours clashing between lamp and fixture
- Very long lifetime of up to 25,000 hours
- COOLFIT functionality - ensures overheat and over temperature protection
- High switching cycles: >100,000
- High colour rendering: CRI80
- Non dimmable
- Warranty: 5 Years



## PRODUCT OVERVIEW

Product name	RefLED Superia Retro ES50 V3 230LM 827 36 SL
Technology	LED
Watt (Rated) (W)	3
Type	LED exchangeable
Cap/Base	GU10
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001959
Warranty	5 years
Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Wattage (W)	3
Product Voltage (V)	230
Dimmable	No
Average life (Nominal) (h)	25000
Product EAN number	5410288291017

## DATA TABLE

### General data

Product name	RefLED Superia Retro ES50 V3 230LM 827 36 SL
Technology	LED
Watt (Rated) (W)	3
Type	LED exchangeable
Cap/Base	GU10
Fixture rating	Open

## RefLED Superia Retro ES50

RefLED Superia Retro ES50 V3 230LM 827 36 SL  
0029101

General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
Operating temperature range (°C)	-20°C...+50°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
Warranty	5 years

### Optical data

Colour temperature (K)	2700
Light colour	Homelight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Luminous Intensity (cd)	500
Beam Angle (°)	36
Photobiological Risk Group	RG1
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	3
Equivalent watt (W)	35
Product Voltage (V)	230
Control gear required	No
No. Of switching cycles before premature failures	>100000
Transformer required	No
Dimmable	No
Inrush Current (A)	5.64
Inrush Duration (µs)	192
Lamp Energy Label (class)	F
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 16A C Breaker	213
Max. Luminaires per 16A B Breaker	128

### Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

### Physical data

Nominal Product Height (mm)	54
Nominal Product Diameter (mm)	50
Weight (kg)	0.05

### Packaging

Single packaging type	Carton
Product EAN number	5410288291017
Packaging single length / height (cm)	8.2

## RefLED Superia Retro ES50


RefLED Superia Retro ES50 V3 230LM 827 36 SL  
0029101

Packaging single width (cm)	6.1
Packaging single depth (cm)	5.1
DUN14 (inner)	25410288291011
Units per inner package	6
Packaging inner length / height (cm)	9.2
Packaging inner width (cm)	16.4
Packaging inner depth (cm)	13.1
DUN14 (outer)	15410288291014
Units per outer package	60
Packaging outer length / height (cm)	20.8
Packaging outer width (cm)	17.8
Packaging outer depth (cm)	68.5


### Safety data

Optimal operating condition (°C)	-20-50
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	None

## PHOTOMETRY



## TECHNICAL DRAWINGS



# SYLVANIA


## RefLED Superia Retro ES50

RefLED Superia Retro ES50 V3 230LM 827 36 SL  
0029101



### SYLVANIA

0029101



**3**  
kWh/1000h




2019/2015

## RefLED Superia Retro ES50

RefLED Superia Retro ES50 V3 230LM 827 36 SL  
0029101



0029101



**3**  
kWh/1000h



2019/2015