

## Micrometer

With V-anvil

Mitutoyo

### Application:

For measuring cutting tools, e.g. screw taps, cutters, reamers.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Friction coupling for consistent, repeatable measuring force
- Prism angle 60°

### Delivery:

Includes box, setting standard, adjustment wrench



<b>Art. no.</b>	<b>32016 450</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	114-108
<b>Min./max. length measuring range</b>	100-115 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface diameter</b>	6.3 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Opening angle</b>	60 Degree
<b>Spindle clamping</b>	Yes
<b>Error limit</b>	8 µm
<b>Display</b>	Nonius
<b>Type</b>	three-flute V-anvil
<b>Calibration Group</b>	D, E
<b>Gross Weight</b>	1.480 kg
<b>Product Group</b>	3MA

### EAN

4946368010038