

# UNITEST DR 100

## Rotary Field Indicator

### Technical Data

Voltage Range	200...440 V
Current Consumption (at Voltage)	< 3.5 mA (440 V)
Frequency Range	45...65 Hz
Operation Time	continuous
Pollution Degree	2
Measurement category	CAT III, 400 V
Safety Complying with	IEC61010/EN61010 IEC61557-7/EN61557-7
Power Supply	from unit under test
Dimensions	110 x 58 x 24 mm
Weight	approx. 150 g



### Key Functions

- Indication of the three phases via glow lamp
- Indication of the phase rotation direction via glow lamp

### General Information

- Swift determination of the phase sequence in three-phase networks

### Order Information:

Description	Cat. No.
UNITESt DR 100	<b>9042</b>
Accessory Set UNIdreh	<b>1324</b>
Carrying Case	<b>1150</b>
Clamp-type test probe for Current Tracks	
red	<b>391511</b>
black	<b>391512</b>

### Accessories:



Accessory Set UNIdreh  
Cat. No. 1324



Carrying Case  
Cat. No. 1150



Clamp-type test probe for Current Tracks  
Cat. No. 391511 (red)  
Cat. No. 391512 (black)



### Scope of Supply:

- 1 pc UNITESt DR 100
- 3 pc Test Probes
- 1 pc Crocodile Clamp
- 1 pc Instruction Manual