


**KEMET Part Number: T491C106K016ZT**  
(B45196E3106K309)

Capacitor, tantalum, 10 uF, 6032, +/-10% Tol, 16V@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
K	1.8	typ
F	2.2	+/-0.1
S	1.3	+/-0.3

**Notes:**

- In polarity stripe, at KEMET's option, type may be indicated: see catalog for explanation of symbols
- Old part number [Obsolete] was B45196E3106K309

**General Information**

Manufacturer:	KEMET
Construction:	Standard Chip-MnO2

**Specifications**

Capacitance:	10 uF
Voltage DC @ 85C:	16V
Voltage DC @ 105C:	13V
Voltage DC @ 125C:	10V
Tolerance:	+/-10%
Application:	General Purpose
Temperature Range:	-55/+125C
Body Type:	Molded Chip
Footprint:	6032
Termination:	Tin
RoHS:	Yes
Leakage Current:	1.6 uA
Dissipation Factor:	6%
Impedance @ 100kHz:	2 Ohm

**Packaging Specifications**

Package Kind:	T&R
Package Size:	7in
Package Quantity:	750