


DCV BENCH METER

Model : DV-101

ISO-9001, CE, IEC1010



FEATURES

- * Digital bench DCV meter, easy operation, professional quality, compact size.
- * Large LCD display.
- * 4 ranges :
 - 200 mV x 0.1 mV
 - 2 V x 0.001 V
 - 20 V x 0.01 V
 - 200 V x 0.1 V
- * High input impedance.
- * Overload protection for each range.
- * Over - input indication.
- * Meet IEC1010 CATII 600V.
- * 006P DC 9V power.
- * Safety standard banana input terminals.
- * Application : Education, Maintenance, Production line, School, Laboratory, Industrial and Quality control.

Lutron

LUTRON ELECTRONIC

The Art of Measurement

DCV BENCH METER

Model : DV-101

FEATURES

- * Easy operation, professional quality, compact size.
- * Application : Education, Maintenance, Production line, School, Laboratory, Industrial and Quality control.

GENERAL SPECIFICATIONS

Display	LCD, 18 mm (0.7") digit height.
Measurement	DC voltage.
Range/ Resolution	200 mV x 0.1 mV
	2 V x 0.001 V
	20 V x 0.01 V
	200 V x 0.1 V
Accuracy	$\pm (0.5\%+1d)$, reading @ 200 mV range
	$\pm (0.8\%+1d)$, reading @ 2V/20 V/200 V range
Input Impedance	10M ohm
Polarity	Automatic Switching '-' indicates negative polarity.
Zero Adjustment	Automatic.
Over - input	display shows '1' or '-1'
Safety	Meet IEC1010 CATII 600V.
Sampling Time	Approx. 0.4 second.
Operating Temperature	0 to 50 °C (32 to 122°F)
Operating Humidity	Less than 80% RH.
Power Supply	006P DC 9V battery.
Power Consumption	Approx. 1.9 mA.
Dimension	147 x 117 x 52 mm, (5.8 x 2.6 x 4.0 inch).
Weight	309 g/0.68 LB (including battery).
Input terminal	Standard banana terminals (Red & Black each).
Standard Accessories	Instruction Manual.....1 PC.

APPLICATIONS

* EDUCATION, SCHOOL & COLLEGES	* LABORATORY
* MAINTENANCE	* INDUSTRIAL
* PRODUCTION LINE	* QUALITY CONTROL

* Appearance and specifications listed in this brochure are subject to change without notice.

CAT-0305-DV101