

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

Trade name : 20G SUPERGLUE HVC16

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

### 1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company  
Site 41  
Knowsthorpe Way  
Cross Green Industrial Estate  
Leeds  
West Yorkshire LS9 0SW  
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

### 1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

---

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

Type of product : Mixture

#### Classification (REGULATION (EC) No 1272/2008)


Skin irritation, Category 2 H315: Causes skin irritation.

Eye irritation, Category 2 H319: Causes serious eye irritation.

Specific target organ toxicity - single exposure, Category 3, Respiratory system H335: May cause respiratory irritation.

### 2.2 Label elements

#### Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms : 

Signal word : Warning

Hazard statements : H315 Causes skin irritation.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017



BUILDING TRUST



Version 2.0

Print Date 03.07.2017

	H319	Causes serious eye irritation.
	H335	May cause respiratory irritation.
Precautionary statements	<b>Prevention:</b>	
	P261	Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
	P280	Wear protective gloves/ eye protection/ face protection.
	<b>Response:</b>	
	P312	Call a POISON CENTER/doctor if you feel unwell.
	P337 + P313	If eye irritation persists: Get medical advice/ attention.
	<b>Storage:</b>	
	P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
	<b>Disposal:</b>	
	P501	Dispose of contents/ container to an approved waste disposal plant.

Hazardous components which must be listed on the label:

- 230-391-5 ethyl 2-cyanoacrylate

### Additional Labelling:

EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

### 2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

## SECTION 3: Composition/information on ingredients

### 3.2 Mixtures

#### Hazardous components

Chemical name CAS-No. EC-No. Registration number	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
ethyl 2-cyanoacrylate 7085-85-0 230-391-5	Eye Irrit.2; H319 STOT SE3; H335 Skin Irrit.2; H315	>= 50 - <= 100
1,4-dihydroxybenzene 123-31-9 204-617-8	Carc.2; H351 Muta.2; H341 Acute Tox.4; H302 Eye Dam.1; H318 Skin Sens.1; H317 Aquatic Acute1; H400	< 0,25

For the full text of the H-Statements mentioned in this Section, see Section 16.

---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

- General advice : Move out of dangerous area.  
Consult a physician.  
Show this safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.  
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.  
Wash off with soap and plenty of water.  
If symptoms persist, call a physician.
- In case of eye contact : Immediately flush eye(s) with plenty of water.  
Remove contact lenses.  
Keep eye wide open while rinsing.  
If eye irritation persists, consult a specialist.
- If swallowed : Do not induce vomiting without medical advice.  
Rinse mouth with water.  
Do not give milk or alcoholic beverages.  
Never give anything by mouth to an unconscious person.

### 4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : Cough  
Respiratory disorder  
Excessive lachrymation  
Erythema  
Dermatitis  
See Section 11 for more detailed information on health effects and symptoms.
- Risks : Causes skin irritation.  
Causes serious eye irritation.  
May cause respiratory irritation.
- irritant effects

### 4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

---

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

- Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017



BUILDING TRUST



Version 2.0

Print Date 03.07.2017

### 5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : No hazardous combustion products are known

### 5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

---

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.  
Deny access to unprotected persons.

### 6.2 Environmental precautions

### 6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).  
Keep in suitable, closed containers for disposal.

### 6.4 Reference to other sections

For personal protection see section 8.

---

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

Advice on safe handling : Do not breathe vapours or spray mist. Avoid exceeding the given occupational exposure limits (see section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

### 7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage : Store in original container. Keep in a well-ventilated place.

areas and containers Containers which are opened must be carefully resealed and kept upright to prevent leakage. Observe label precautions. Store in accordance with local regulations.

Other data : No decomposition if stored and applied as directed.

**7.3 Specific end use(s)**

Specific use(s) : No data available

**SECTION 8: Exposure controls/personal protection**

**8.1 Control parameters**

**Components with workplace control parameters**

Components	CAS-No.	Value	Control parameters *	Basis *
ethyl 2-cyanoacrylate	7085-85-0	STEL	0,3 ppm 1,5 mg/m3	GB EH40
1,4-dihydroxybenzene	123-31-9	TWA	0,5 mg/m3	GB EH40

**8.2 Exposure controls**

**Personal protective equipment**

Eye protection : Safety glasses with side-shields  
 Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.

Suitable for short time use or protection against splashes:  
 Butyl rubber/nitrile rubber gloves (0,4 mm),  
 Contaminated gloves should be removed.  
 Suitable for permanent exposure:  
 Viton gloves (0.4 mm),  
 breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.

Respiratory protection : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe work-

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017



BUILDING TRUST



Version 2.0

Print Date 03.07.2017

ing limits of the selected respirator.  
organic vapor filter (Type A)  
A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm  
Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

---

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

Appearance	: liquid
Colour	: colourless
Odour	: slight
Odour Threshold	: No data available
Flash point	: ca. 80 °C
Autoignition temperature	: Not applicable
Decomposition temperature	: No data available
Lower explosion limit (Vol-%)	: No data available
Upper explosion limit (Vol-%)	: No data available
Flammability	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available
pH	: No data available
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: No data available
Vapour pressure	: No data available
Density	: ca. 1,05 g/cm <sup>3</sup> at 20 °C
Water solubility	: soluble

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017

Version 2.0

Print Date 03.07.2017



BUILDING TRUST



Partition coefficient: n-octanol/water	:	No data available
Viscosity, dynamic	:	No data available
Viscosity, kinematic	:	> 7 mm <sup>2</sup> /s at 40 °C
Relative vapour density	:	No data available
Evaporation rate	:	No data available

### 9.2 Other information

No data available

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

No dangerous reaction known under conditions of normal use.

### 10.2 Chemical stability

The product is chemically stable.

### 10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

### 10.4 Conditions to avoid

Conditions to avoid : No data available

### 10.5 Incompatible materials

Materials to avoid : No data available

### 10.6 Hazardous decomposition products

---

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

Not classified based on available information.

#### Components:

##### 1,4-dihydroxybenzene:

Acute oral toxicity : Acute toxicity estimate: 500 mg/kg  
Method: Converted acute toxicity point estimate

#### Skin corrosion/irritation

Causes skin irritation.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017



BUILDING TRUST



Version 2.0

Print Date 03.07.2017

### Serious eye damage/eye irritation

Causes serious eye irritation.

### Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

### Germ cell mutagenicity

Not classified based on available information.

### Carcinogenicity

Not classified based on available information.

### Reproductive toxicity

Not classified based on available information.

### STOT - single exposure

May cause respiratory irritation.

### STOT - repeated exposure

Not classified based on available information.

### Aspiration toxicity

Not classified based on available information.

---

## SECTION 12: Ecological information

### 12.1 Toxicity

#### Components:

#### 1,4-dihydroxybenzene :

M-Factor (Acute aquatic toxicity) : 10

### 12.2 Persistence and degradability

No data available

### 12.3 Bioaccumulative potential

No data available

### 12.4 Mobility in soil

No data available

### 12.5 Results of PBT and vPvB assessment

#### Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

### 12.6 Other adverse effects



**Product:**

Additional ecological information : There is no data available for this product.

---

**SECTION 13: Disposal considerations**

**13.1 Waste treatment methods**

Product : The generation of waste should be avoided or minimized wherever possible.  
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.  
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.  
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.  
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10\* packaging containing residues of or contaminated by dangerous substances

---

**SECTION 14: Transport information**

**ADR**

Not dangerous goods

**IATA**

**14.1 UN number** : 3334  
**14.2 UN proper shipping name** : Aviation regulated liquid, n.o.s. (ethyl 2-cyanoacrylate)  
**14.3 Transport hazard class(es)** : 9  
Labels : 9  
**14.5 Environmental hazards** : no

**IMDG**

Not dangerous goods

**14.6 Special precautions for user**

No data available

**14.7 Transport in bulk according to Annex II of Marpol and the IBC Code**

Not applicable

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017



BUILDING TRUST



Version 2.0

Print Date 03.07.2017

### SECTION 15: Regulatory information

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

##### Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed (=> 0.1 %).

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

REACH Information: All substances contained in our Products are  
- preregistered or registered by our upstream suppliers, and/or  
- preregistered or registered by us, and/or  
- excluded from the regulation, and/or  
- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.  
Not applicable

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations  
Health and Safety at Work Act 1974 & Subsidiary Regulations  
Control of Substances Hazardous to Health Regulations (COSHH)  
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

#### 15.2 Chemical safety assessment

This product contains substances for which Chemical Safety Assessments are still required.

### SECTION 16: Other information

#### Full text of H-Statements

H302 Harmful if swallowed.  
H315 Causes skin irritation.  
H317 May cause an allergic skin reaction.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

## 20G SUPERGLUE HVC16

Revision Date 03.07.2017

Version 2.0

Print Date 03.07.2017



BUILDING TRUST



H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H341	Suspected of causing genetic defects.
H351	Suspected of causing cancer.
H400	Very toxic to aquatic life.

### Full text of other abbreviations

Acute Tox.	Acute toxicity
Aquatic Acute	Acute aquatic toxicity
Carc.	Carcinogenicity
Eye Dam.	Serious eye damage
Eye Irrit.	Eye irritation
Muta.	Germ cell mutagenicity
Skin Irrit.	Skin irritation
Skin Sens.	Skin sensitisation
STOT SE	Specific target organ toxicity - single exposure
ADR	Accord européen relatif au transport international des marchandises Dangereuses par Route
CAS	Chemical Abstracts Service
DNEL	Derived no-effect level
EC50	Half maximal effective concentration
GHS	Globally Harmonized System
IATA	International Air Transport Association
IMDG	International Maritime Code for Dangerous Goods
LD50	Median lethal dosis (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
LC50	Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
MARPOL	International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	Occupational Exposure Limit
PBT	Persistent, bioaccumulative and toxic
PNEC	Predicted no effect concentration
REACH	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	Substances of Very High Concern
vPvB	Very persistent and very bioaccumulative

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

|| Changes as compared to previous version !