


SD5600



Compressed air meter

SDR14DGXFRKG/US-100



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Measuring range	0.8...250 l/min	0.3...82.9 m/s	0.05...15 m³/h
Process connection	threaded connection G 1/4 DN8		

Application

Application	for industrial applications		
Media	Argon (Ar); carbon dioxide (CO ₂); nitrogen (N ₂); air		
Medium temperature [°C]	-10...60		
Min. bursting pressure [bar]	64		
Pressure rating [bar]	16		

Electrical data

Operating voltage [V]	18...30 DC; (according to EN 50178 SELV/PELV)		
Current consumption [mA]	< 80		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	1		



Compressed air meter

SDR14DGXFRKG/US-100

Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1		
Inputs			
Inputs	counter reset		
Outputs			
Output signal	switching signal; analogue signal; pulse signal; IO-Link; (configurable)		
Electrical design	PNP/NPN		
Number of digital outputs	2		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2.5		
Permanent current rating of switching output DC [mA]	150; (per output)		
Number of analogue outputs	1		
Analogue current output [mA]	4...20; (scalable)		
Max. load [Ω]	500		
Pulse output	consumed quantity meter		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	0.8...250 l/min	0.3...82.9 m/s	0.05...15 m³/h
Display range	0...300 l/min	0...99.5 m/s	0...18 m³/h
Resolution	0.2 l/min	0.1 m/s	0.01 m³/h
Set point SP	2.2...249.9 l/min	0.7...82.9 m/s	0.13...14.99 m³/h
Reset point rP	0.9...248.7 l/min	0.3...82.5 m/s	0.06...14.92 m³/h
Analogue start point ASP	0...200 l/min	0...66.3 m/s	0...12 m³/h
Analogue end point AEP	50...250 l/min	16.6...82.9 m/s	3...15 m³/h
Low flow cut-off LFC	0.3...2.7 l/min	0.1...0.9 m/s	0.02...0.16 m³/h
In steps of	0.1 l/min	0.1 m/s	0.01 m³/h
Pressure monitoring			
Measuring range [bar]	-1...16		
Display range [bar]	-1...20		
Resolution [bar]	0.05		
Set point SP [bar]	-0.92...16		
Reset point rP [bar]	-1...15.92		
Analogue start point [bar]	-1...12.8		
Analogue end point [bar]	2.2...16		
In steps of [bar]	0.01		

SD5600



Compressed air meter

SDR14DGXFRKG/US-100

Volumetric flow quantity monitoring		
Measuring range	0...100000000 m ³	0...353146667.2 scf
Display range	0...100000000 m ³	0...353146667.2 scf
Set point SP	0.001...10000000 m ³	0.05...353146667.2 scf
Pulse value	0.001...10000000 m ³	0.05...353146667.2 scf
In steps of	0.0001 m ³	0.005 scf
Pulse length [s]	0.01...2	
Temperature monitoring		
Measuring range	-10...60 °C	14...140 °F
Display range	-24...74 °C	-11.2...165.2 °F
Resolution	0.2 °C	0.5 °F
Set point SP	-9.7...60 °C	14.6...140 °F
Reset point rP	-10...59.7 °C	14...139.4 °F
Analogue start point	-10...46 °C	14...114.8 °F
Analogue end point	4...60 °C	39.2...140 °F
In steps of	0.1 °C	0.1 °F
Accuracy / deviations		
Temperature coefficient [1/K]	± 0,07 % MW	
Accuracy (in the measuring range)	± (6 % MW + 0,6 % MEW); at medium temperature 23 °C	
Repeatability	0,8 % MW + 0,2 % MEW	
Pressure monitoring		
Repeatability [% of the final value]	± 0,2	
Characteristics deviation [% of the final value]	< ± 0,5; (BFSL = Best Fit Straight Line)	
Greatest TEMPCO of the span [% MEW / 10 K]	± 0,15	
Greatest TEMPCO of the zero point [% MEW / 10 K]	± 0,25	
Temperature monitoring		
Accuracy [K]	± 0,5; (medium flow in the limit area of the flow measurement range)	
Response times		
Response time [s]	0.1; (dAP = 0)	
Damping for the switching output dAP [s]	0...5	
Pressure monitoring		
Response time [s]	0.05	
Temperature monitoring		
Dynamic response T05 / T09 [s]	T09 = 0,5	
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser	

SD5600



Compressed air meter

SDR14DGXFRKG/US-100

Interfaces	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9 CDV
IO-Link device ID	861 d / 00 03 5d h
Profiles	Digital Measuring Sensor (0x800A), Identification and Diagnosis (0x4000)
SIO mode	yes
Required master port type	A
Process data analogue	8
Process data binary	2
Min. process cycle time [ms]	7.2

Operating conditions	
Ambient temperature [°C]	0...60
Storage temperature [°C]	-20...85
Max. relative air humidity [%]	90
Protection	IP 65; IP 67

Tests / approvals		
EMC	DIN EN 60947-5-9	
Vibration resistance	DIN EN 68000-2-6	5 g (10...2000 Hz)
MTTF [years]	183	
UL approval	UL Approval no.	I012
	File number UL	E174189
Pressure Equipment Directive	Sound engineering practice; can be used for stable gases fluid group 2	

Mechanical data	
Weight [g]	558
Materials	PBT+PC-GF30; PPS GF40; stainless steel (1.4301 / 304); stainless steel (1.4305 / 303); steel (1.5523) galvanised; 2.0401 (brass / CW614N); FKM
Materials (wetted parts)	EN AW-6082 (aluminium); stainless steel (1.4305 / 303); FKM; ceramics glass passivated; PPS GF40; Al ₂ O ₃ (ceramics); acrylate
Process connection	threaded connection G 1/4 DN8

Displays / operating elements	
Display	colour display 1,44", 128 x 128 pixels 2 x LED, yellow

Remarks	
Remarks	MW = measured value MEW = Final value of the measuring range Standard conditions: 1013.25 mbar / 15 °C / 0 % relative humidity For information about installation and operation please see the operating instructions.
Pack quantity	1 pcs.

Electrical connection	
Connector:	1 x M12

SD5600




Compressed air meter

SDR14DGXFRKG/US-100



Connection



OUT1/IO-Link: switching output flow
 switching output temperature
 switching output pressure
 Pulse output quantity meter
 signal output Preset counter

OUT2/InD: switching output flow
 switching output temperature
 switching output pressure
 analogue output flow
 analogue output temperature
 analogue output pressure
 signal output Preset counter
 Pulse output quantity meter
 input counter reset