

Proportional flow control valve, 2-way version

RE 29190/02.07 Replaces: 02.06

1/12

Type 2FRE

Sizes 10 and 16 Component series 4X Maximum operating pressure 315 bar Maximum flow 160 l/min




Table of contents


Contents Page Features 1 Ordering code 2 - For subplate mounting: 2 Standard types 3 Symbols Function, section 3 4, 5 Technical data Electrical connection, cable sockets 6 Characteristic curves 7 to 9 Unit dimensions 10, 12 electronics

Features

- Valve with pressure compensator for the pressure-compensated control of a flow
- Actuation by means of proportional solenoid
- Porting pattern to ISO 6263, see page 10 Subplates according to data sheet RE 45066
 - (separate order), see page 10
- With electrical closed-loop position control of the metering
 - The position transducer coil can be axially shifted, which
 - simplifies zero point balancing of the metering orifice (electrical-hydraulic) without the need for intervening into the control
 - Low manufacturing tolerances of the valve and the electrical amplifier types VT-VRPA1-151-1X (analogue) and amplifier module Typ VT-MRPA1-151-1X (analogue), separate order, see page 5
 - Flow control in both directions due to rectifier sandwich plate

Information on available spare parts: www.boschrexroth.com/spc

Ordering code: Proportional flow control valve



Nominal flow $A \rightarrow B$ / flow characteristics						
Size 10			Size 16			
Linear		Progressive with ra (fine control r		Linear		
Up to 10 l/min Up to 16 l/min Up to 25 l/min Up to 50 l/min Up to 60 l/min	= 10L = 16L = 25L = 50L = 60L	With rapid speed	= 5Q = 10Q	Up to 80 l/min Up to 100 l/min Up to 125 l/min Up to 160 l/min	= 80L = 100L = 125L = 160L	

Standard types


Size 10

Туре	material number
2FRE 10-4X/10LBK4M	R900915817
2FRE 10-4X/16LBK4M	R900915825
2FRE 10-4X/25LBK4M	R900915820
2FRE 10-4X/50LBK4M	R900915815

Size 16

Туре	material number		
2FRE 16-4X/100LBK4M	R900915819		
2FRE 16-4X/160LBK4M	R900915814		

Ordering code: Rectifier sandwich plate



Size 10

Туре	material number		
Z4S 10-2X/	R900413377		
Z4S 10-2X/V	R900413379		


Size 16

Туре	material number		
Z4S 16-2X/	R900425901		
Z4S 16-2X/V	R900427362		

Symbols

Proportional flow control valve

Simplified





Detailed

Rectifier sandwich plate

 \bigcirc = component side,







Function, section

Proportional flow control valves of type 2FRE ... feature a 2-way function. They can control a flow, which is determined by an electrical command value, in a pressure- and largely temperature-compensated way.

They basically consist of housing (1), proportional solenoid with inductive position transducer (2), metering orifice (3), pressure compensator (4), stroke limiter (5) and check valve (6).

The setting of the flow is determined by the setting (0 to 100 %) on the command value potentiometer. The selected command value causes metering orifice (3) to be adjusted via the amplifier and the proportional solenoid. The inductive position transducer senses the position of metering orifice (3). Any deviations from the command value are corrected by the closed-loop position control.

Pressure compensator (4) keeps the pressure differential across metering orifice (3) always at a constant value. This ensures pressure compensation of the flow.

If the current regulator is used only within a range, which is significantly smaller than the maximum nominal flow provided from the valve, the response time of pressure compensator (4) can be shortened by limiting the pressure compensator stroke. Thus, undesirable start-up jumps can be reduced.

If the grub screw of stroke limiter (5) is at the left-hand limit stop (turned out), the pressure compensator stroke is not limited.

The low temperature drift is a result of the favourable design of the metering orifice.


At a command value of 0 % the metering orifice is closed.

In the event of a power failure or cable break on the inductive position transducer, the metering orifice closes.

Starting from a 0 % command value, a jump-free start-up is possible. The metering orifice can be opened and closed with a delay provided by two ramps in the electrical amplifier.

Check valve (6) allows the free return flow from B to A.

The supply and return flow to and from the actuator can be controlled with the help of an additional rectifier sandwich plate of type Z4S... under the proportional flow control valve.



Technical data (for applications outside these parametes, please consult us!)

Size		Size			10				1	6	
Weight	- Proportional flow control valve	kg	6.1			8.	.5				
	- Rectifier sandwich plate	kg			3.2				9.	.3	
Installation orientation	on					(Optiona	.I			
Storage temperatur	e range	°C	- 20 to + 80								
Ambient temperatur	e range	°C	- 20 to + 70								
Hydraulic - prop	ortional flow control valve (measured	d with HL	P46 and	d at $artheta_{\scriptscriptstyle 0}$	= 40	°C ± 5 '	°C)				
Size		Size			10				1	6	
Max. operating pressure	in port A	bar			,	U	p to 31	5			
Max. flow	- Linear	l/min	10	16	25	50	60	80	100	125	160
	- Progressive with rapid speed	l/min	,		40				_	-	
Minimum pressure of	differential	bar			3 to 8				6 to	10	
Δp with free flow B	→ A	bar	see diagram on page 9								
Flow control	,										
Temperature drift	– Hydraulic + electrical $\Delta q_{_{ m V}}$ /°C	%	% 0.1 of q_{Vmax}								
	- Pressure-compensated (up to $\Delta p = 315$ bar)	%	\pm 2 of q_{Vmax}								
Hydraulic fluid			Mineral oil (HL, HLP) to DIN 51524 Further hydraulic fluids on enquiry!								
Hydraulic fluid temp	erature range	°C				- 2	0 to +	80			
Viscosity range		mm²/s			,	15	5 to 38	0			
•	gree of contamination of the hyness class to ISO 4406 (c)		Class 20/18/15 ¹⁾								
Hysteresis		%				<±	1 of <i>q</i> ₁	/max			
Repeatability		%	< 1 of q _{Vmax}								
Manufacturing tolerance	Valve	%	% $\leq \pm 2$ at 33 % command value $\leq \pm 5$ at 100 % command value								
	- Amplifier VT-VRPA1-151 (analogue)	%	Amplifier must be matched to valve ²⁾								
	- Amplifier module VT-MRPA1-151 (analogue)	%	% Amplifier must be matched to valve ²⁾								
Hydraulic - recti	fier sandwich plate										
Size		Size			10				1	6	
Operating pressure bar			Up to 315								
Cracking pressure	cking pressure bar			1.5							
			I/min 60 160								

¹⁾ The cleanliness classes specified for components must be adhered to in hydraulic systems. Effective filtration prevents malfunction and, at the same time, prolongs the service life of components.

For the selection of filters, see data sheets RE 50070, RE 50076, RE 50081, RE 0086 and RE 50088.

²⁾ Due to tolerances of the oscillator frequency (position transducer supply), amplifiers are subject to tolerances. When installing new systems or replacing an amplifier, the amplifier settings may have to be adjusted.

Technical data (for applications outside these parametes, please consult us!)

Type of voltage			DC				
Coil resistance - Cold value at 20 °C		Ω	10				
	– Max. hot value	Ω	13.9				
Duty cycle		%	100				
Max. current per so	lenoid	Α	1.51				
Electrical connection	on		With component plu	g to DIN EN 175301	-803-A		
			Cable socket to DIN EN 175301-803-A 1)				
Type of protection	to EN 60529		IP 65 ²⁾ , with cable socket mounted and locked				
Electrical – indu	ctive position transducer						
Coil resistance	Total resistance of coils betwe	en	1 and 2	2 and ≟	≟ and 1		
at 20 °C (see page 6)		Ω	31.5	45.5	31.5		
Electrical connection			With component plug GSA20				
			Cable socket GM209N (Pg 9) 1)				
Inductance		mH	6 to 8				
Oscillator frequenc	у	kHz	2.5				
Electrical position r	neasuring system		Differential throttle				
Nominal stroke mm		mm	4				
Type of protection to EN 60529			IP 65 ²⁾ , with cable socket mounted and locked				
Control electro	onics (separate order)						
Associated amplifier in Euro-card format			Type VT-VRPA1-151-1X (analogue) to data sheet RE 30118				


¹⁾ Separate order, see page 6

²⁾ Due to the surface temperatures of solenoid coils, observe European standards DIN EN563 and DIN EN982!


Electrical connection, cable sockets (nominal dimensions in mm)

Proportional solenoid


Connection to component plug




Connection to cable socket




Cable socket to DIN EN 175301-803-A Separate order stating material no. **R901017011** (plastic version)







Inductive position transducer




Cable socket Pg 9 Separate order stating material no. **R900013674**(plastic version)







Characteristic curves (measured at $v=41~\rm mm^2/s$ and $\vartheta=50~\rm ^{\circ}C$; $\rho_{\rm nom}=50~\rm bar$; Amplitude 0 \rightarrow 100 %; size 10 type 60L / size 16 type 160L)

Transient function at stepped command value change






Frequency response characteristic curves





Frequency in Hz →


Characteristic curves (measured at $v = 41 \text{ mm}^2/\text{s}$ and $\vartheta = 50 \text{ °C}$)

Dependence of flow on command value voltage (flow control from $\mbox{\bf A} \rightarrow \mbox{\bf B})$












Characteristic curves (measured at $v = 41 \text{ mm}^2\text{/s}$ and $\vartheta = 50 \text{ °C}$)


Pressure differential across check valve $B \rightarrow A$





Leakage flow from $A \rightarrow B$







Rectifier sandwich plate

Pressure differential identical in both directions of flow

12 Slze 10 10 8 6 4 2 0 10 20 30 40 50 60 Flow in I/min →




Unit dimensions: Proportional flow control valve (nominal dimensions in mm)




B1 B2	95	123.5
D0		
DZ	76	101.5
В3	9.5	11
B4	79.4	102.4
B5	-	0.8
B6	97	126
B7	10.5	12
ØD1	9	11
ØD2	15	18
H1	245	255.5
H2	200	210
Н3	210	140
H4	48	51

Size	10	16
L1	102.5	123.5
L2	82.5	101.5
L3	10	11
L4	24	31
L5	62.5	72.5
L6	23.8	28.6
L7	105	126
L8	11	12



- 1 Valve housing
- 2 Proportional solenoid with inductive position transducer
- 3.1 Cable socket for proportional solenoid; separate order, see page 6
- **3.2** Cable socket for position transducer (separate order, see page 6)
 - 4 Space required to remove cable socket
 - 5 Setscrew of pressure compensator limiter, hexagon socket A/F 3, lock nut A/F 10
 - 6 Valve fixing screws (separate order, see page 11)
 - 7 Identical seal rings for ports A and B
 - 8 Port A
 - 9 Port B
- 10.1 Locating pin for sizes 10 and 16
- 10.2 Locating pin for size 16

Required surface quality of the valve contact face



Tolerances to: - General tolerances ISO 2768-mK

- 11.1 Locating bore for locating pin for sizes 10 and 16
- 11.2 Locating bore for locating pin for size 16
 - 13 Nameplate
 - Machined valve mounting face,Size 10 position of ports to ISO 6263-06-05-0-97Size 16 position of ports to ISO 6263-09-05-0-97

Subplates to data sheet RE 45066 and valve fixing screws must be ordered separately.

 Subplates:
 Size 10
 Size 16

 G279/01 (G1/2)
 G281/01 (G1)

 G280/01 (G3/4)
 G282/01 (G1 1/4)

Unit dimensions: Valve fixing screws (separate order)

Without rectifier sandwich plate

Size 10

The following valve fixing screws are recommended:

4 socket head cap screws to ISO 4762 - M8 x 60 - 10.9-flZn-240h-L (Friction coefficient 0.09 to 0.14 to VDA 235-101); tightening torque M_T = 30 Nm \pm 10%,

material no. R913000217

or

4 socket head cap screws to ISO 4762 - M8 x 60 - 10.9

(Friction coefficient 0.08 to 0.6 to VDI2230, tempering, black);

tightening torque $M_{\rm T} = 34 \text{ Nm} \pm 10\%$

Size 16

The following valve fixing screws are recommended:

4 socket head cap screws to ISO 4762 - M10 x 70 - 10.9-flZn-240h-L (Friction coefficient 0.09 to 0.14 to VDA 235-101); tightening torque $M_{\rm T}=64$ Nm \pm 10%, material no. R913000126

01

4 socket head cap screws to ISO 4762 - M10 x 70 - 10.9 (Friction coefficient 0.08 to 0.16 to VDI 2230, tempering, black);

tightening torque $M_T = 75 \text{ Nm} \pm 10\%$,

With rectifier sandwich plate

Size 10

The following valve fixing screws are recommended:

4 socket head cap screws to ISO 4762 - M8 x 120 - 10.9-flZn-240h-L (Friction coefficient 0.09 to 0.14 to VDA 235-101); tightening torque $M_{\rm T}=$ 30 Nm \pm 10%, material no. R913000423

٥r

4 socket head cap screws to ISO 4762 - M8 x 120 - 10.9

(Friction coefficient 0.08 to 0.16 to VDI2230,

tempering, black);

tightening torque $M_{\rm T} = 34 \text{ Nm} \pm 10\%$

Size 16

The following valve fixing screws are recommended:

4 socket head cap screws to ISO 4762 - M10 x 160 - 10.9-flZn-240h-L (Friction coefficient 0.09 to 0.14 to VDA 235-101); tightening torque $M_{\rm T}=64$ Nm \pm 10%, material no. R913000072

or


4 socket head cap screws to ISO 4762 - M10 x 160 - 10.9

(Friction coefficient 0.08 to 0.6 to VDI 2230,


tempering, black);

tightening torque $M_T = 75 \text{ Nm} \pm 10\%$,

Unit dimensions: Rectifier sandwich plate (nominal dimensions in mm)



Size	10	16
B1	95	123.5
B2	76	101.5
B3	9.5	11
B4	79.4	102.4
B5	_	0.8
ØD1	9	11
H5	60	85
H6	30	40
L1	102.5	123.5
L2	82.5	101.5
L3	10	11
L6	23.8	28.6



Required surface quality of valve contact face

Tolerances to:

- General tolerances ISO 2768-mK

- 1 Valve housing
- Valve fixing screws (separate order, see page 11)
- 7 Identical seal rings for A and B
- 8 Port A1 (A2)
- 9 Port B1 (B2)
- 10 Locating pin (position like items 11.1 and 11.2)
- 11.1 Locating bore for locating pin for sizes 10 and 16
- **11.2** Locating bore for locating pin for size 6
 - 12 Rectifier sandwich plate
- 13.1 Nameplate (rectifier sandwich plate size 10)
- 13.2 Nameplate (rectifier sandwich plate size 16)
 - 15 Subplate (separate order)

Subplates to data sheet RE 45066 and valve fixing screws must be ordered separately.

must be ordered separately.

Subplates: Size 10 Size 16

G279/01 (G1/2) G281/01 (G1) G280/01 (G3/4) G282/01 (G1 1/4)

Bosch Rexroth AG
Hydraulics
Zum Eisengießer 1
97816 Lohr am Main, Germany
Phone, +49 (0) 93 52 / 18-0
Fax +49 (0) 93 52 / 18-23 58
documentation@boschrexroth.de

www.boschrexroth.de

© This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth AG. It may not be reproduced or given to third parties without its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.