


EVW105



Connection cable

VDOGF040SCS01,5T04STGF040SCS



Application

| | |
|--------------------|--|
| Special feature | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Application | welding applications |
| Free from silicone | yes |

Electrical data

| | |
|-----------------------------|-------------------|
| Operating voltage [V] | < 50 AC / < 60 DC |
| Protection class | III |
| Max. current load total [A] | 3 |

Operating conditions

| | |
|--------------------------------------|-----------------------------|
| Ambient temperature [°C] | -25...90 |
| Note on ambient temperature | cULus: ...85 |
| Ambient temperature (moving) [°C] | -25...90 |
| Note on ambient temperature (moving) | cULus: ...85 |
| Protection | IP 65; IP 67; IP 68; IP 69K |

EVW105



Connection cable

VDOGF040SCS01,5T04STGF040SCS

| Mechanical data | | |
|------------------------|---|--|
| Weight [g] | 60 | |
| Materials | housing: TPU orange; Sealing: FKM | |
| Material nut | brass, anti-spatter / brass, anti-spatter | |
| Drag chain suitability | yes | |
| Drag chain suitability | bending radius for flexible use | min. 10 x cable diameter |
| | travel speed | max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s ² |
| | bending cycles | > 2 Mio. |
| | torsional strain | ± 180 °/m |

| Remarks | |
|---------------|-----------------------|
| Remarks | without label holders |
| Pack quantity | 1 pcs. |

Electrical connection - plug


Connector: 1 x M8, straight; Locking: brass, anti-spatter; Contacts: gold-plated; Tightening torque: 0.3...0.5 Nm



Electrical connection

Cable: 1.5 m, PUR, Halogen-free, grey, Ø 4.5 mm; not irradiated (can be recycled); resistant to welding sparks; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Connection



Electrical connection - socket

Connector: 1 x M8, straight; Locking: brass, anti-spatter; Contacts: gold-plated; Tightening torque: 0.3...0.5 Nm

EVW105



Connection cable

VDOGF040SCS01,5T04STGF040SCS

