



CONTACTOR,AC3:37KW/400V, 1NO+1NC, 20-33V AC/DC, WITH VARISTOR, 3-POLE, SIZE S2, SPRING-TYPE TERMINAL

Figure similar

|                     |                |
|---------------------|----------------|
| product brand name  | SIRIUS         |
| Product designation | 3RT2 contactor |

General technical data:

|   |    |            |
|---|----|------------|
| <b>Insulation voltage</b>   |    |            |
| • Rated value   | V  | 690        |
| <b>Degree of pollution</b>  |    | 3          |
| <b>Surge voltage resistance Rated value</b>   | kV | 6          |
| <b>Mechanical service life (switching cycles)</b>                                   |    |            |
| • of the contactor typical  |    | 10 000 000 |
| • of the contactor with added electronics-compatible auxiliary switch block typical |    | 5 000 000  |
| • of the contactor with added auxiliary switch block typical                        |    | 10 000 000 |
| <b>Thermal short-time current restricted to 10 s</b>                                | A  | 640        |
| <b>Protection class IP</b>  |    |            |
| • on the front  |    | IP20       |
| • of the terminal   |    | IP00       |
| <b>Equipment marking</b>  |    |            |
| • acc. to DIN EN 61346-2  |    | Q          |
| • acc. to DIN EN 81346-2  |    | Q          |

Main circuit:

|   |  |   |
|---|--|---|
| <b>Number of poles for main current circuit</b> |  | 3 |
| <b>Number of NC contacts for main contacts</b>  |  | 0 |
| <b>Number of NO contacts for main contacts</b>  |  | 3 |
| <b>Operating voltage</b>                        |  |   |

|   |   |      |
|---|---|------|
| • at AC-3 Rated value maximum                             | V | 690  |
| <b>Operating current</b>                                  |   |      |
| • at AC-1   |   |      |
| — at 400 V at ambient temperature 40 °C<br>Rated value    | A | 90   |
| — up to 690 V at ambient temperature 40 °C<br>Rated value | A | 90   |
| — up to 690 V at ambient temperature 60 °C<br>Rated value | A | 80   |
| • at AC-2 at 400 V Rated value                            | A | 80   |
| • at AC-3   |   |      |
| — at 400 V Rated value                                    | A | 80   |
| — at 500 V Rated value                                    | A | 80   |
| — at 690 V Rated value                                    | A | 58   |
| • at AC-4 at 400 V Rated value                            | A | 55   |
| <b>Operating current with 1 current path</b>              |   |      |
| • at DC-1   |   |      |
| — at 24 V Rated value                                     | A | 75   |
| — at 110 V Rated value                                    | A | 4.5  |
| — at 220 V Rated value                                    | A | 2    |
| — at 440 V Rated value                                    | A | 0.4  |
| — at 600 V Rated value                                    | A | 0.25 |
| • at DC-3 at DC-5   |   |      |
| — at 24 V Rated value                                     | A | 35   |
| — at 110 V Rated value                                    | A | 2.5  |
| — at 220 V Rated value                                    | A | 2    |
| — at 440 V Rated value                                    | A | 0.1  |
| — at 600 V Rated value                                    | A | 0.06 |
| <b>Operating current with 2 current paths in series</b>   |   |      |
| • at DC-1   |   |      |
| — at 24 V Rated value                                     | A | 75   |
| — at 110 V Rated value                                    | A | 45   |
| — at 220 V Rated value                                    | A | 5    |
| — at 440 V Rated value                                    | A | 1    |
| — at 600 V Rated value                                    | A | 0.8  |
| • at DC-3 at DC-5   |   |      |
| — at 110 V Rated value                                    | A | 25   |
| — at 220 V Rated value                                    | A | 5    |
| — at 24 V Rated value                                     | A | 55   |
| — at 440 V Rated value                                    | A | 0.27 |
| — at 600 V Rated value                                    | A | 0.16 |
| <b>Operating current with 3 current paths in series</b>   |   |      |

|  |     |           |
|--|-----|-----------|
| <ul style="list-style-type: none"> <li>• at DC-1 <ul style="list-style-type: none"> <li>— at 24 V Rated value</li> <li>— at 110 V Rated value</li> <li>— at 220 V Rated value</li> <li>— at 440 V Rated value</li> <li>— at 600 V Rated value</li> </ul> </li> <li>• at DC-3 at DC-5 <ul style="list-style-type: none"> <li>— at 110 V Rated value</li> <li>— at 220 V Rated value</li> <li>— at 24 V Rated value</li> <li>— at 440 V Rated value</li> <li>— at 600 V Rated value</li> </ul> </li> </ul> | A   | 55        |
|  | A   | 45        |
|  | A   | 45        |
|  | A   | 2.9       |
|  | A   | 1.4       |
|  | A   | 45        |
|  | A   | 25        |
|  | A   | 55        |
|  | A   | 0.6       |
|  | A   | 0.6       |
| <b>Operating power</b>   |     |           |
| <ul style="list-style-type: none"> <li>• at AC-1 at 400 V Rated value</li> <li>• at AC-2 at 400 V Rated value</li> <li>• at AC-4 at 400 V Rated value</li> </ul>   | kW  | 59        |
|  | kW  | 37        |
|  | kW  | 30        |
| <b>Operating power</b>   |     |           |
| <ul style="list-style-type: none"> <li>• at AC-1 <ul style="list-style-type: none"> <li>— at 230 V at 60 °C Rated value</li> <li>— at 230 V Rated value</li> <li>— at 400 V at 60 °C Rated value</li> <li>— at 690 V at 60 °C Rated value</li> <li>— at 690 V Rated value</li> </ul> </li> <li>• at AC-3 <ul style="list-style-type: none"> <li>— at 230 V Rated value</li> <li>— at 400 V Rated value</li> <li>— at 500 V Rated value</li> <li>— at 690 V Rated value</li> </ul> </li> </ul>            | kW  | 28        |
|  | kW  | 34        |
|  | kW  | 49        |
|  | kW  | 85        |
|  | kW  | 102       |
|  | kW  | 22        |
|  | kW  | 37        |
|  | kW  | 37        |
|  | kW  | 45        |
| <b>Operating power for ≥ 200000 operating cycles at AC-4</b>   |     |           |
| <ul style="list-style-type: none"> <li>• at 400 V Rated value</li> <li>• at 690 V Rated value</li> </ul>   | kW  | 15.8      |
|  | kW  | 21.8      |
| <b>Operating frequency</b>   |     |           |
| <ul style="list-style-type: none"> <li>• at AC-3 maximum</li> </ul>  | 1/h | 500       |
| <b>Control circuit/ Control:</b>   |     |           |
| <b>Type of voltage of the control supply voltage</b>   |     | AC/DC     |
| <b>Control supply voltage with AC</b>  |     |           |
| <ul style="list-style-type: none"> <li>• at 50 Hz Rated value</li> <li>• at 60 Hz Rated value</li> </ul>   | V   | 20 ... 33 |
|  | V   | 20 ... 33 |
| <b>Control supply voltage for DC</b>   |     |           |
| <ul style="list-style-type: none"> <li>• Rated value</li> </ul>  | V   | 20 ... 33 |

|   |   |               |
|---|---|---------------|
| <b>Operating range factor control supply voltage rated value of the magnet coil with AC</b> |   |               |
| • at 50 Hz  |   | 0.8 ... 1.1   |
| • at 60 Hz  |   | 0.8 ... 1.1   |
| <b>Operating range factor control supply voltage rated value of the magnet coil for DC</b>  |   | 0.8 ... 1.1   |
| <b>Design of the surge suppressor</b>   |   | with varistor |
| <b>Closing power of the magnet coil for DC</b>  | W | 23            |
| <b>Holding power of the magnet coil for DC</b>  | W | 1             |

#### Auxiliary circuit:

|  |   |   |
|--|---|---|
| <b>Number of NC contacts</b>                         |   |   |
| • for auxiliary contacts                             |   |   |
| — instantaneous contact                              |   | 1   |
| <b>Number of NO contacts</b>                         |   |   |
| • for auxiliary contacts                             |   |   |
| — instantaneous contact                              |   | 1   |
| <b>Product expansion Auxiliary switch</b>            |   | Yes   |
| <b>Operating current at AC-15</b>                    |   |   |
| • at 230 V Rated value                               | A | 10  |
| • at 400 V Rated value                               | A | 3   |
| • at 690 V Rated value                               | A | 1   |
| <b>Operating current</b>                             |   |   |
| • at DC-12 at 125 V Rated value                      | A | 2   |
| • at DC-12 at 220 V Rated value                      | A | 1   |
| • at DC-12 at 600 V Rated value                      | A | 0.15  |
| • at DC-13 at 125 V Rated value                      | A | 0.9   |
| • at DC-13 at 220 V Rated value                      | A | 0.3   |
| • at DC-13 at 600 V Rated value                      | A | 0.1   |
| <b>Operating current</b>                             |   |   |
| • at DC-12   |   |   |
| — at 60 V Rated value                                | A | 6   |
| — at 110 V Rated value                               | A | 3   |
| • at DC-13   |   |   |
| — at 24 V Rated value                                | A | 10  |
| — at 60 V Rated value                                | A | 2   |
| — at 110 V Rated value                               | A | 1   |
| <b>Contact reliability of the auxiliary contacts</b> |   | 1 faulty switching per 100 million (17 V, 1 mA) |

#### UL/CSA ratings:

|   |   |    |
|---|---|----|
| <b>Full-load current (FLA) for three-phase AC motor</b> |   |    |
| • at 480 V Rated value                                  | A | 65 |
| • at 600 V Rated value                                  | A | 62 |

|  |           |             |
|--|-----------|-------------|
| <b>yielded mechanical performance [hp]</b>   |           |             |
| <ul style="list-style-type: none"> <li>• for single-phase AC motor at 110/120 V Rated value</li> </ul> | metric hp | 5           |
| <ul style="list-style-type: none"> <li>• for single-phase AC motor at 230 V Rated value</li> </ul>     | metric hp | 15          |
| <ul style="list-style-type: none"> <li>• for three-phase AC motor at 200/208 V Rated value</li> </ul>  | metric hp | 20          |
| <ul style="list-style-type: none"> <li>• for three-phase AC motor at 220/230 V Rated value</li> </ul>  | metric hp | 25          |
| <ul style="list-style-type: none"> <li>• for three-phase AC motor at 460/480 V Rated value</li> </ul>  | metric hp | 50          |
| <ul style="list-style-type: none"> <li>• for three-phase AC motor at 575/600 V Rated value</li> </ul>  | metric hp | 60          |
| <b>Contact rating of the auxiliary contacts acc. to UL</b>   |           | A600 / P600 |

#### Short-circuit:

|   |  |  |
|---|--|--|
| <b>Design of the fuse link</b>  |  |  |
| <ul style="list-style-type: none"> <li>• for short-circuit protection of the main circuit <ul style="list-style-type: none"> <li>— with type of assignment 1 required</li> <li>— with type of assignment 2 required</li> </ul> </li> <li>• for short-circuit protection of the auxiliary switch required</li> </ul> |  | gL/gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 250 A<br>gL/gG NH 3NA, DIAZED 5SB, NEOZED 5SE: 160 A<br>fuse gL/gG: 10 A |

#### Installation/ mounting/ dimensions:

|   |    |  |
|---|----|--|
| <b>mounting position</b>  |    | +/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface |
| <b>Mounting type</b>  |    | screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022   |
| <ul style="list-style-type: none"> <li>• Side-by-side mounting</li> </ul>   |    | Yes  |
| <b>Height</b>   | mm | 113.4  |
| <b>Width</b>  | mm | 55   |
| <b>Depth</b>  | mm | 130  |
| <b>Required spacing</b>   |    |  |
| <ul style="list-style-type: none"> <li>• with side-by-side mounting <ul style="list-style-type: none"> <li>— forwards</li> <li>— Backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— Backwards</li> <li>— upwards</li> <li>— at the side</li> </ul> </li> </ul> | mm | 0<br>0<br>0<br>0<br>0<br><br>0<br>0<br>50<br>6   |

|                  |    |    |
|------------------|----|----|
| — downwards      | mm | 50 |
| • for live parts |    |    |
| — forwards       | mm | 0  |
| — Backwards      | mm | 0  |
| — upwards        | mm | 50 |
| — downwards      | mm | 50 |
| — at the side    | mm | 6  |

#### Connections/ Terminals:

|  |     |  |
|--|-----|--|
| <b>Type of electrical connection</b>                     |     |  |
| • for main current circuit                               |     | screw-type terminals   |
| • for auxiliary and control current circuit              |     | spring-loaded terminals  |
| <b>Type of connectable conductor cross-section</b>       |     |  |
| • for main contacts                                      |     |  |
| — single or multi-stranded                               |     | 2x (1 ... 35 mm <sup>2</sup> ), 1x (1 ... 50 mm <sup>2</sup> ) |
| — finely stranded with core end processing               |     | 2x (1 ... 25 mm <sup>2</sup> ), 1x (1 ... 35 mm <sup>2</sup> ) |
| • for AWG conductors for main contacts                   |     | 2x (18 ... 2), 1x (18 ... 1)                                   |
| • for auxiliary contacts                                 |     |  |
| — single or multi-stranded                               |     | 2x (0,5 ... 2,5 mm <sup>2</sup> )                              |
| — finely stranded with core end processing               |     | 2x (0,5 ... 1,5 mm <sup>2</sup> )                              |
| — finely stranded without core end processing            |     | 2x (0,5 ... 2,5 mm <sup>2</sup> )                              |
| • for AWG conductors for auxiliary contacts              |     | 2x (20 ... 14)   |
| <b>Apparent pick-up power of the magnet coil with AC</b> |     |  |
| • at 50 Hz   | V·A | 40   |
| • at 60 Hz   | V·A | 40   |

#### Safety related data:

|  |   |  |
|--|---|--|
| <b>Proportion of dangerous failures</b>                      |   |  |
| • with low demand rate acc. to SN 31920                      | % | 40   |
| • with high demand rate acc. to SN 31920                     | % | 73   |
| <b>Product function Mirror contact acc. to IEC 60947-4-1</b> |   | Yes  |
| <b>Protection against electrical shock</b>                   |   | finger-safe when touched vertically from front acc. to IEC 60529 |

#### Mechanical data:

|                          |  |    |
|--------------------------|--|----|
| <b>Size of contactor</b> |  | S2 |
|--------------------------|--|----|

#### Ambient conditions:

|  |    |             |
|--|----|-------------|
| <b>Installation altitude at height above sea level maximum</b> | m  | 2 000       |
| <b>Ambient temperature</b>                                     |    |             |
| • during operation   | °C | -25 ... +60 |
| • during storage   | °C | -55 ... +80 |

## Certificates/ approvals:

General Product Approval

other



[Confirmation](#)

[Environmental  
Confirmations](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RT20383NB30>


**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3RT20383NB30/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3RT20383NB30&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3RT20383NB30&lang=en)





last modified:

11.03.2015