Panasonic Digital Noise Filters

Coil type EMI Filters (DNF) SMD

Japan

Series: **E**Type: **-**


■ Features

- 3218 case size, 2 A rated current.
- No variation in attenuation characteristics as current changes.
- Stable P/N marking using laser technology.
- Marking is on the top face of product. Easy P/N marking confirmation after assembly on PWB.

■ Recommended Applications

• Data lines, secondary power supply lines (DC lines) for game, digital AV and communications equipment.

■ Explanation of Part Numbers



■ Typical Specification


● Operating temperature : -20 to +85 °C

■ Rated Voltage : DC 50 V (Except ELKEA333FA : DC25 V)

Rated Current : DC 2 A

• Reliability characteristics endurance (High Temp.)

Soldering condition (reflow) : 85 $^{\circ}$ C 50 V 2 A 1000 h (Spec : 500 h)




■ Standard Parts

Part No.	Cut off frequency (MHz)	Inner Capacitance (pF typ.)	Rated Voltage (V)	Rated Current (A)	Indication	Min, Packaging unit (pcs.)
ELKE100FA	250	10			100□	
ELKE220FA	200	22	50	2.0	220□	2000
ELKE470FA	100	47			470□	
ELKE101FA	50	100			101□	
ELKE221FA	25	220			221□	
ELKE471FA	10	470			471□	
ELKE102FA	5	1000			102□	
ELKE222FA	2	2200			222□	
ELKE103FA	0.5/DC	10000			103□	
ELKE333FA	0.2/DC	33000	25		333□	


note1 : 4th letter (\square) of marking indicates the Month Code.

Panasonic Digital Noise Filters


■ Indication Examples




■ Land Pattern in mm (not to scale)




■ Dimensions in mm (not to scale)




■ Equivalent circuit, measurement block diagram



■ Performance characteristics (Reference)



■ Packaging state



Pulling direction

Reel Size : ϕ 178

Q'ty : 2000 pcs./Reel Packaging : Embossed taping