

High-performance angular milling cutter 90° with weld-on shank

For indexable milling inserts AD.X 0602..

ATORN[®]



Advantage

- Highly positive indexable insert
- Low power consumption
- Precise 90° angular milling

Art. No.	16030 004
Cutting edge diameter	12 mm
Clearance length	25 mm
Length	70 mm
Shaft diameter	12 mm
max. ap	5.5 mm
Number of cutting edges	2 PCS

EAN-Code

4050293388862