

## THE WRECKER sabre saw blade with carbide teeth



### Execution:

- The multi-material WRECKER™ sabre saw blade with carbide-tipped teeth cuts everything from thick metal and cast iron to wood containing nails, hardened screws or bolts.
- Up to 50x longer tool life compared to standard bi-metal sabre saw blades. Carbide-tipped teeth for a longer service life and outstanding durability in the toughest applications.
- Optimised for use with cordless sabre saws: Up to 25 % more cuts per battery charge compared to standard bi-metal saw blades.
- FANG TIP™ immersion point for fast plunge cuts.
- 1.27 mm thick blade for precise straight cuts.
- 25 mm high blade for greater stability and reduced vibration.
- Ideal for demolition work involving multiple materials



<b>Art. no.</b>	<b>70800 646</b>
<b>Brand</b>	MILWAUKEE
<b>Manufacturer Part Number</b>	48005701
<b>Length</b>	150 mm
<b>Cutting material</b>	Bimetal
<b>Number of teeth per inch</b>	7 / 11
<b>Cut</b>	Fast cut
<b>Gross Weight</b>	0.174 kg
<b>Product Group</b>	7MC

### EAN

045242082476