



Flexo Print

TL 100W/10-R UV-A

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the 'R' lamps in the family have an internal 200-degree reflector to further optimize the lamp's overall efficiency.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		
Main Application	Phototherapy		
Life to 50% Failures (Nom)	2000 h		
Useful Life (Nom)	1000 h		
Light Technical			
Color Code	10-R		
Color Designation	Ultra Violet A		
Chromaticity Coordinate X (Nom)	220		
Chromaticity Coordinate Y (Nom)	200		
UV Depreciation at 500 h	10 %		
UV Depreciation at 1000 h	20 %		
UV Depreciation at 2000 h	30 %		

Operating and Electrical	
Power (Nom)	100 W
Lamp Current (Nom)	0.97 A
Voltage (Nom)	122 V
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
UV	
UV-B/UV-A (IEC)	0.1 %
UV-A Radiation 100Hr (IEC)	26.0 W
UV-A Radiation OHr (IEC)	28.0 W
Product Data	
Full product code	871150061281640
Order product name	TL 100W/10-R UV-A


Datasheet, 2020, November 10 data subject to change

Flexo Print

EAN/UPC - Product	8711500612816
Order code	928006901029
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25

Material Nr. (12NC)	928006901029
Net Weight (Piece)	391.600 g


Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 100W/10-R UV-A	40.5 mm	1763.8 mm	1770.9 mm	1768.5 mm	1778 mm

TL 100W UV-A 1R

Photometric data



XDPO_XUVATL_10-R-Spectral power distribution Colour



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.