

ICP401835TPRT

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V Safety Circuit, NTC

Specifications

Renata Type IEC Designation Part Number Contact Method: Safety Circuit

Nominal Voltage Typical Capacity Minimum Capacity ICP401835 ICP051937 101026 Wire AWG 30 Yes, incl. NTC

3.7 V 215 mAh 205 mAh (0.2C cut off 3.0 V at 20°C)

Internal Impedance

Thickness (t) Lenghth (l) Width (w) Weight

Charging Characteristic

Voltage Current Normal Max. Charging Current Temperature at Charging

Discharge Characteristic

Cut off Voltage Max discharge Current

Temperature during Discharge

Cycle Life at Room Temperature

Storage Temperature

< 320 mΩ / 30% SOC

Max 4.4 mm (after 500 cycles) Max 37.0 mm (after 500 cycles) Max 18.2 mm (after 500 cycles) ~ 5.4 g




Illustration only. For detailed drawing please contact your sales representative.

CC/CV – Constant Current / Constant Voltage 4.2 V CV 0.5 C CC – 107.5 mA 1.0 C CC – 215 mA 0 °C 45 °C

3.0 V2.0 C - 430 mA (for non continues discharge) 1.0 C - 215 mA (for continues discharge) $-20 \ ^{\circ}C \dots \ 60 \ ^{\circ}C$

> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)

-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the ASDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage www.renata.com/downloads/restriction_of_use

Renata SA CH-4452 Itingen/Switzerland Tel. +41 (0)61 975 75 75 Fax. +41 (0)61 975 75 95 sales@renata.com www.renata.com Rev. ICP401835TPRT V01 11/2022

