




PRIMARY VOLTAGE

Protection	Reference	Secondary voltage V	Secondary Current mA	No-load voltage V	Ambient Temperature °C	Rating VA
	44157	6	383	10,5	T 70 B	2,3
	44158	9	256	15,7	T 70 B	2,3
	44159	12	192	21	T 70 B	2,3
	44160	15	153	25,9	T 70 B	2,3
	44161	18	128	31,4	T 70 B	2,3
	44162	24	96	41,9	T 70 B	2,3
	44163	2 x 6	2 x 192	2 x 10,5	T 70 B	2,3
	44164	2 x 9	2 x 128	2 x 15,7	T 70 B	2,3
	44165	2 x 12	2 x 96	2 x 21	T 70 B	2,3
	44166	2 x 15	2 x 77	2 x 25,9	T 70 B	2,3
	44167*	2 x 18	2 x 64	2 x 31,4	T 70 B	2,3
	44168*	2 x 24	2 x 48	2 x 41,9	T 70 B	2,3



* **to be noted** : 2 x 18 V and 2 x 24 non safety transformer approved, conform to EN 61558-2-6 (Isolating transformer).

- Vacuum filling
- Two compartments bobbins
- Self-extinguishing plastics UL 94 VO
- Degree of protection IP 00
- 70 grams weight
- Resin class B CEI 85 (20 000 h testing to CEI 126)
- Inherently short-circuits proof
- 30 V model is VDE EN 61558-2-6 certified (production on request)
- Insulation voltage 4 KV (6 KV MYRRA test)
- 100% tested production
- Certification : CCA procedure on request

1 Secondary winding



2 Secondary windings



Recommended layout for transformers with 1 secondary winding (Allows the use of a transformer with 2 secondary winding)

