

Collet type ER

Application:

For drilling and centring tools.

Execution:

- For NC lathes
- Burnished
- For suitable collets, see no. 23320
- No. 23308 008-020 ring profile key for tightening and loosening.

Art. no.	22782 028
Brand	EWS
Manufacturer Part Number	135934
VDI mount diameter	20 mm
Collet type	ER 32
Min./max. clamping range	2-20 mm
Projecting length	60 mm
Outer diameter	50 mm
Gross Weight	0.600 kg
Product Group	215

