

62261-1 ✓ ACTIVE

FASTON | FASTON 250

TE Internal #: 62261-1

FASTON 250, PCB Terminals, Tab, Tab, PCB Terminal Mating Tab

Width .25 in [6.35 mm], PCB Terminal Mating Tab Thickness .032 in [.81 mm]

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



Terminal & Splice Type: **Tab**

PCB Terminal Terminal Type: **Tab**

PCB Terminal Mating Tab Width: **6.35 mm [.25 in]**

PCB Terminal Mating Tab Thickness: **.81 mm [.032 in]**

PCB Hole Diameter: **3.3 mm [.13 in]**

Features

Product Type Features

Insertion Force	Normal
FASTON	Yes
PCB Terminal Mounting Style	Stud Mount
Terminates To	Printed Circuit Board

Configuration Features

Stud Hole	Yes
Terminal Angle	90°

Body Features

PCB Terminal Plating Material	Unplated
-------------------------------	----------

Contact Features

Terminal & Splice Type	Tab
PCB Terminal Terminal Type	Tab
Underplating Material	None
Terminal Size	6.35



PCB Terminal Terminal Orientation	Right Angle
-----------------------------------	-------------

Termination Features

PCB Terminal Termination Method	Screw
---------------------------------	-------

Dimensions

Stud Diameter	3.3 mm[.13 in]
---------------	----------------

PCB Terminal Mating Tab Width	6.35 mm[.25 in]
-------------------------------	-----------------

PCB Terminal Mating Tab Thickness	.81 mm[.032 in]
-----------------------------------	-----------------

PCB Hole Diameter	3.3 mm[.13 in]
-------------------	----------------

Height Above PC Board	10.79 mm[.425 in]
-----------------------	-------------------

Usage Conditions

Insulation Requirement	Uninsulated
------------------------	-------------

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

CSA Certified	Yes
---------------	-----

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	1000
--------------------	------

PCB Terminal Packaging Method	Bag
-------------------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | FASTON 250



Customers Also Bought





TE Part #1393030-7
P&B SSR SERIES SOLID STATE RELAYS



TE Part #142241-1
250 FASTON,TAB,BR

Documents

Product Drawings

FASTON .250 SERIES (6.3 MM) TAB BR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_62261-1_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62261-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_62261-1_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTON Tabs

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English