


# DI5023



## Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US



1 potentiometer



### Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range [mm]		10
Housing		threaded type
Dimensions [mm]		M30 x 1.5 / L = 92.3

### Application

Application	simple evaluation of rotating and linear movement with regard to underspeed; blocking
-------------	---

### Electrical data

Nominal voltage DC [V]	10...36
Current consumption [mA]	< 20
Protection class	III
Reverse polarity protection	yes

### Outputs

Total number of outputs	1
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Short-time current rating of switching output [mA]	250
Short-circuit proof	yes
Overload protection	yes

### Detection zone

Sensing range [mm]	10
Sensing range adjustable	no
Operating distance [mm]	0...8.1

## Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US

<b>Measuring/setting range</b>		
Setting range	[Imp/min]	5...3600
<b>Accuracy / deviations</b>		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
<b>Response times</b>		
Start-up delay	[s]	15
Max. damping frequency	[Imp/min]	18000
<b>Software / programming</b>		
Adjustment of the switch point		multiturn potentiometer
<b>Operating conditions</b>		
Ambient temperature	[°C]	-25...80
Protection		IP 65; IP 67
<b>Tests / approvals</b>		
EMC		EN 60947-5-2
Shock resistance		DIN EN 60947-5-2
Vibration resistance		DIN EN 60947-5-2
MTTF	[years]	3262
<b>Mechanical data</b>		
Weight	[g]	252
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 92.3
Thread designation		M30 x 1.5
Materials		brass special coating; PA; stainless steel; TPE-U
Tightening torque	[Nm]	50
<b>Displays / operating elements</b>		
Display	switching status	1 x LED, green
<b>Accessories</b>		
Accessories (supplied)		lock nuts: 2
<b>Electrical connection</b>		
Connector: 1 x M12		



## Compact evaluation unit for speed monitoring

DIA3010-ZPKG/US

### Connection

