



**Part no.: 50003190**  
**TK 40x180**  
**Reflector**

Figure can vary

## Contents

- Technical data

Part no.: 50003190 – TK 40x180 – Reflector

## Technical data

<b>Mechanical data</b>	
Design	Rectangular
Mounting dimension, width	41 mm
Reflection surface width	36 mm
Mounting dimension, height	181 mm
Reflection surface height	176 mm
Mounting dimension, thickness	8.2 mm
Triple reflector size	3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	39 g
Type of fastening	Through-hole mounting

<b>Environmental data</b>	
Ambient temperature, operation	-40 ... 65 °C

<b>Certifications</b>	
Degree of protection	IP 67

<b>Classification</b>	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467