


PRODUCT RANGE (RATINGS @ 85°C)				
TYPE	CONTINUOUS		TRANSIENT	
	RMS VOLTAGE (VOLTS)	DC VOLTAGE (VOLTS)	ENERGY (10/1000µs) (JOULES)	PEAK CURRENT (8/20µs) (AMPS)
DVS24	30	38	8.8	1000
DVS48	60	81	20	4500
DVS110	150	200	80	6500
DVS240	275	350	151	8000

SPECIFICATION

LINE FREQUENCY 50/60 Hz
 TEMPERATURE RANGE -25C TO +85C
 WIRE GUAGE 12 AWG
 MOUNTING EN 50 022 RAIL (TOP HAT)
 SCREW TERMINALS 2.5sq.mm (12 AWG)

ELECTRICAL CONNECTION



EXAMPLE

