

EAN CODE : 3760244880192

24V

ALF2401

PRATICAL : ON/OFF switch.

- Power-on indicator.



PRECISE : Output ripple < 3mV rms.

- Output voltage adjustable from 20 to 30V.

PROTECTED : against Short circuit.**RESISTANT TO SHOCK****30 WATTS**

24V (Adj. 20 to 30V)

1,25A

**Specifications****Voltage**

- Floating outputs on 4 mm safety sockets.
- Output voltage : adjustable from 20 to 30V. Delivered to 24V \pm 1%
- Regulation : < 20mV for a load variation from 0 to 100%
< 5mV for a line variation from 190 to 264V.
- Ripple : < 3mV rms including:
< 3mV peak to peak of the switching signal
< 4mV peak to peak of the signal at 100 Hz
< 15mV peak to peak of switching spikes
- Dynamic regulation : <0,5% for a load variation from 10 to 90%
- Indicator : green power-on LED indicator.

Current

- Max I : 1,5A to 20V
1,25A to 24V
1A to 30V

Power

- Max output power : 30W.
- Efficiency : >82% at the full power (30W in output)

Protection

- Against short circuit protection, by current limit.
- Against overcurrent on main input, by fuse.
- Against transient pulse on the primary by varistor.

Other specifications

- Safety : Class II, Safety Extra Low Voltage (SELV) according to EN 61010-1.
- EMC : Complies with EN 61326-1, performance criteria B, and EN 55011, ISM Group I, Class B.
- Protection level : IP 30.
- Input voltage : 190 to 264 Volts, 50 / 60 Hz.
- Mains input : C8 socket with CEI320 C7 removable cable (2 poles double insulation).
- Power consumption : 35 W max.
- ON/OFF control : toggle switch
- Dielectric strength : 3000 Vac between input and output.
- Presentation : polycarbonate case screenprinted.