



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 125 °C

Expanded Inside Diameter (Min): 5.97 mm [.235 in]

Recovered Inside Diameter (Max): 2.79 mm [.11 in]

Pre-Installed Lead: No

Wire Temperature (Max): 85 °C

Features

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

Expanded Inside Diameter (Min)	5.97 mm [.235 in]
Recovered Inside Diameter (Max)	2.79 mm [.11 in]

Usage Conditions

Operating Temperature (Max)	125 °C
Wire Temperature (Max)	85 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought



TE Part #207464-7
HDP-20,PLUG,SIZE 3, 25 POSN



TE Part #165008
PLASTI-GRIP, SPADE 22-16 8



TE Part #1-770248-0
UMNL II PIN SN/AUNI/BR LP



TE Part #1-794611-1
MICRO MNL RPT CNT,LS PC,15AU,L




TE Part #1-794612-1
PIN CONT 20-24 15 GOLD L/P



TE Part #1241396-3
AMP MCP 2.8K, CONTACT, SWS



TE Part #184355-2
2X2 CAP ASSEMBLY, B KEY, GRAY,



TE Part #2-1333204-7
ANVIL, COMBINATION (.080)



Documents

Product Drawings

[B-155-9004](#)

English

Datasheets & Catalog Pages

[Raychem Electrical Interconnect Products](#)

English