



BA9s,24V DC -15%/+10% buzzer, pulsed tone



Powering Business Worldwide™

Part no.
Article no.

M22-XAMP
229028

83 dB/10 cm, 18 - 30 mA, positive pole connected to X1, f = 2300 Hz

Program

Range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Single unit/Complete unit			Single unit
Description			83 dB/10 cm, 18 - 30 mA, positive pole at X1, f = 2300 Hz
Function			Pulsed tone, 24 V DC (+10 %/-15 %)
Front ring			Front ring: titanium
For use with			BA9s base
Connection to SmartWire-DT			no

Approbationen

UL approval	Yes
CSA approval	Yes
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CE marking
UL File No.	E29184
UL CCN	NKCR
CSA File No.	012528
CSA Class No.	3211-03
NA Certification	UL listed, CSA certified

Technical data according to ETIM 4.0

Operational voltage at DC			24
Type of acoustic signal			Pulsed tone
Voltage type			DC
Operating voltage at AC 60 Hz		V	24
Operating voltage at AC 50 Hz		V	24

CAD-Data

Product standards CAD data: <http://eaton-moeller.partcommunity.com>

Additional product information (links)

Engineering

Key to part numbers	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/TYPENSCHLUESSEL_RM-Q-TITAN_de.pdf
Engineering	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/PRO_RM-Q-Titan_D_de.pdf
Ordering example for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/Bestellbeispiel_F0315_COMBINATION_de.pdf
Order form for custom complete units	ftp://ftp.moeller.net/DOCUMENTATION/PDF/GB/FORM_F0315_Combination_de.pdf