

INSAVER SLIM SQUARE 200

Insaver Slim Square UGR19 200 IP44 2400lm 840

0030315

Product features

- Insaver Slim is a ceiling recessed LED downlight (IP44 from the front), Die-cast aluminium body, loop in loop out connector for quick installation, Non dimmable LED driver, 20W; 2400lm; 120lm/W; 4000K; UGR <19 with shallow product depth 65mm. Meets TP(a) requirements.



PRODUCT OVERVIEW

Product name	Insaver Slim Square UGR19 200 IP44 2400lm 840
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Office, Retail
ETIM Class	EC001744
E-number FI	4276930
Warranty	5 years
Fixture luminous flux (lm)	2400
Luminaire efficacy (lm/W)	120
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	60
Beam Angle (°)	NA
Glare control	< 19
Photobiological Risk Group	RG1
Total power consumption (W)	20
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9003 - Signal white
IP rating	IP44/20
IK rating	IK07
Product EAN number	5410288303154

DATA TABLE

INSAVER SLIM SQUARE 200

Insaver Slim Square UGR19 200 IP44 2400lm 840

0030315

General data

Product name	Insaver Slim Square UGR19 200 IP44 2400lm 840
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Ceiling recessed mounting
General application	Hospitality, Office, Retail
Operating temperature range (°C)	-10°C...+40°C
Performance ambient temperature Tq (°C)	40
ETIM Class	EC001744
E-number FI	4276930
Warranty	5 years

Optical data

Fixture luminous flux (lm)	2400
Luminaire efficacy (lm/W)	120
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	60
Beam Angle (°)	NA
Distribution type	Symmetric
Glare control	< 19
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	20
Mains voltage (V)	220-240V
Lamp power factor	0.9
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class II
Control gear type	LED driver constant current
No. Of switching cycles before premature failures	>100000
Dimmable	No
Dimming method	N/A
Drive current (mA)	600
Inrush Current (A)	17.2
Inrush Duration (µs)	200
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	20
Max. Luminaires per 13A C Breaker	26
Max. Luminaires per 16A C Breaker	32

INSAVER SLIM SQUARE 200

Insaver Slim Square UGR19 200 IP44 2400lm 840

0030315

Max. Luminaires per 20A C Breaker	40
Max. Luminaires per 10A B Breaker	12
Max. Luminaires per 13A B Breaker	15
Max. Luminaires per 16A B Breaker	19
Max. Luminaires per 20A B Breaker	24

Lifetime data

Lifespan L70 B50	90000
Lifespan L80 B20	90000
Lifespan L90 B10	39000

Physical data

Housing colour	RAL 9003 - Signal white
IP rating	IP44/20
IK rating	IK07
Diffuser finish	Other
Diffuser material	None
Reflector finish	Silver
Nominal Product Length (mm)	217
Nominal Product Width (mm)	217
Nominal Product Height (mm)	60
Cutout Dimensions (W x L in mm or Diameter in mm)	200
Weight (kg)	0.8
Recessed Depth (mm)	150

Packaging

Single packaging type	Carton
Product EAN number	5410288303154
Packaging single length / height (cm)	25.0
Packaging single width (cm)	25.0
Packaging single depth (cm)	8.0
DUN14 (outer)	15410288303151
Units per outer package	12
Packaging outer length / height (cm)	51.5
Packaging outer width (cm)	51.5
Packaging outer depth (cm)	26.0


Safety data

Optimal operating condition (°C)	-10-40
----------------------------------	--------

PHOTOMETRY


INSAVER SLIM SQUARE 200

Insaver Slim Square UGR19 200 IP44 2400lm 840
0030315



0.5	0.57	E(0°) E(C0)	29.5°	888 297
1.0	1.13	E(0°) E(C0)	29.5°	222 73
1.5	1.70	E(0°) E(C0)	29.5°	98 32
2.0	2.26	E(0°) E(C0)	29.5°	55 18
2.5	2.83	E(0°) E(C0)	29.5°	38 12
3.0	3.39	E(0°) E(C0)	29.5°	27 9

Distance [m] Cone diameter [m] Illuminance [lx]
C0 - C180 (Half beam angle: 55.0°)



TECHNICAL DRAWINGS

