27.7










ECOLVB

Electrical connection

Dimensions



40.5

Model number

VAZ-G10-TERM

Passive bus termination G10

Features


- Ultra-compact enclosure
- Extension of strand length to over 200 m
- · Two different impedances integrated
- Suitable for all topologies
- Two-stage voltage monitor and display for AS-Interface and AUX
- · Gold-plated and machined contacts
- Degree of protection IP68 / IP69K

Function

The passive terminator VAZ-G10-TERM in the G10-design includes two different terminations in one housing. With the two terminators, all topologies of an AS-Interface network can be terminated. The termination resistor Z1 offers the right impedance for most topologies. The termination resistor Z2 is used when Z1 does not reach the required signal quality improvement.

Two LEDs per terminator monitor the status of each supply voltage. On the bus termination, the voltage is shown in 2 stages. The free flat cable channel can be used to monitor the external power supply U_{AUX} .

Indicating / Operating means




www.pepperl-fuchs.com

echnical data eneral specifications AS-Interface specification	
General specifications AS-Interface specification	
AS-Interface specification	
rie mieriaes opeemeanen	V3.0
UL File Number	E223772 "For use in NFPA 79 Applications only"
ndicators/operating means	
LED green	AS-Interface voltage > 26 V: LED lights
LED yellow	AS-Interface voltage > 18.5 V: LED lights
Electrical specifications	
Rated operating voltage U _e	, 18.5 31.6 V
Rated operating current I _e	≤ 15 mA per connection
Protection class	III
Ambient conditions	
Ambient temperature	-25 70 °C (-13 158 °F)
Storage temperature	-25 85 °C (-13 185 °F)
Shock and impact resistance	30~g, 11 ms in 6 spatial directions 3 shocks $10~g$, 16 ms in 6 spatial directions 1000 shocks
Vibration resistance	0.75 mm 10 57 Hz , 5 g 57 150 Hz, 20 cycles
Mechanical specifications	
Degree of protection	IP67 IP67 / IP68 / IP69K with flat cable VAZ-FK-S-*
Connection	via Flat cable
Material	
Housing	PBT PC
Mounting screw	Stainless steel 1.4305 / AISI 303
Mass	100 g
Tightening torque, fastening screws	1.65 Nm
Compliance with standards and directed and control of the control	ecti-
Directive conformity	
EMC Directive 2004/108/EC	EN 61326:2006
Standard conformity	
Noise immunity	EN 61000-6-2:2005, EN 61326-1:2006, EN 50295:1999
Emitted interference	EN 61000-6-4:2007
Degree of protection	EN 60529:2000
Fieldbus standard	EN 50295:1999, IEC 62026-2:2006
Approvals and certificates	
UL approval	cULus Listed, Type 1 enclosure
Maximum permissible ambient temp ture	pera- ≤ 65 °C (≤ 149 °F)

Notes

Mounting instructions

You may screw the device onto a level mounting surface using two M4 attachment screws. The attachement screws are not included.



Purpose

Improvement of signal quality and voltage monitoring.

Operation on the most remote AS-Interface strand.

Maximum 2 repeaters in line possible.

When using repeaters please check if a terminator is integrated.