

MWLN clamp holder, negative, left

For copy, longitudinal and face turning with WN indexable insert

ATORN[®]

Application

For copy, longitudinal and face turning with WN indexable insert, 80°.

Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type W, working angle 93°, tip angle 80°, clearance angle 0°

Advantage

- Triple-edge geometry lowers cost per cut
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- Adjustable clamp minimises vibrations and ensures good force transfer



Art. No.	17860 035
ISO name	MWLN R/L 2525 M06
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Programming size	32 mm
Length of head	25 mm
Suitable for indexable inserts	WN.. 0604..
Tool design	Left
DIN	4983

EAN-Code

4050293 127096