

RJ45 socket insert - CUC-IND-J1ST-A/R4LS - 1091946

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




RJ45 socket insert, type: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, connection method: Solder connection

Your advantages

- ✓ Design perfectly matched to the RJ45 INDUSTRIAL connector for reliable connectivity
- ✓ Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- ✓ 360° shielding ensures reliable transmission, even in industrial applications
- ✓ Enables data transmission speeds of up to 10 Gbps in accordance with CAT6A
- ✓ Automated handling process thanks to reflow capability
- ✓ Tray packing



Key Commercial Data

Packing unit	84 pc
Minimum order quantity	84 pc
GTIN	 4 055626 906355
GTIN	4055626906355
Weight per Piece (excluding packing)	5.700 g
Custom tariff number	85366930
Note	Made to Order (non-returnable)

Technical data

Mechanical characteristics

Connection method	Solder connection
Number of slots	1
Rated voltage (III/2)	72 V DC
Rated surge voltage (III/3)	1.5 kV
Overvoltage category	II

RJ45 socket insert - CUC-IND-J1ST-A/R4LS - 1091946

Technical data

Mechanical characteristics

Insertion/withdrawal cycles	> 750
Number of positions	8
Degree of pollution	2
Weight	5.7 g

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Material data

Contact surface material	AU
Contact material	Copper alloy
Width	16.2 mm
Height	16.5 mm
Length	17.1 mm
Mounting type	PCB mounting

Electrical characteristics

Number of positions	8
GRP transmission properties	Data transmission 10 Gbps
Transmission speed	10 Gbps
Rated current	1.5 A
Overvoltage category	II
Degree of pollution	2
Test voltage Core/Core	1000 V
Test voltage Core/Shield	1500 V

Standards and Regulations

Halogen-free	yes
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 9.0	27440205
------------	----------

ETIM

ETIM 5.0	EC000438
----------	----------

Approvals

Approvals

RJ45 socket insert - CUC-IND-J1ST-A/R4LS - 1091946

Approvals

Approvals

EAC / UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

EAC			B.01742
UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 335024
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 335024
cULus Recognized			

Accessories

Accessories

Data plug

RJ45 connector - CUC-IND-C1ZNI-S/R4IE10G8 - 1149846



RJ45 connector, IP20, CAT6_A, 8-pos., with IDC fast connection technology, for AWG 26 - 24 1-wire, 7-wire, and 19-wire conductors

RJ45 connector - CUC-IND-C1ZNI-S/R4IP10G8 - 1149847



RJ45 connector, IP20, CAT6_A, 8-pos., with IDC fast connection technology, for AWG 23 - 22 1-wire, 7-wire, and 19-wire conductors

RJ45 socket insert - CUC-IND-J1ST-A/R4LS - 1091946

Accessories

RJ45 connector - CUC-IND-C1ZNI-S/R4IP8 - 1421126



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 23- 22, cable outlet: straight, color: green

RJ45 connector - CUC-IND-C1ZNI-S/R4IE8 - 1421607



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: straight, color: green

RJ45 connector - CUC-IND-C1ZNI-S/R4QV6 - 1406335



RJ45 connector, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: straight, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly

RJ45 connector - CUC-IND-C1ZNI-T/R4IE8 - 1421877



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: angled

RJ45 connector - CUC-IND-C1ZNI-B/R4IE8 - 1421876



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: angled

RJ45 socket insert - CUC-IND-J1ST-A/R4LS - 1091946

Accessories

RJ45 connector - CUC-IND-C1ZNI-B/R4QV6 - 1406338



RJ45 connector, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: angled, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly

RJ45 connector - CUC-IND-C1ZNI-T/R4QV6 - 1406341



RJ45 connector, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 26- 24, cable outlet: angled, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly

RJ45 connector - CUC-IND-C1ZNI-B/R4IP8 - 1421127



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 23- 22, cable outlet: angled

RJ45 connector - CUC-IND-C1ZNI-T/R4IP8 - 1421128



RJ45 connector, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Zinc die-cast, connection method: IDC fast connection, connection cross section: AWG 23- 22, cable outlet: angled