

UL-No. E235797

Werkstoff:
 E-CU sn = Elektrolytkupfer verzinkt

Temperaturbeständigkeit:
 bis +125°C


Matière:
 E-CU sn = cuivre électrolytique étamé

Résistant à une température:
 jusqu'à +125°C

Material:
 E-CU sn = tin-plated electrolytic copper

Temperature range:
 up to +125°C

| mm ² | AWG | Artikelnummer Numéro d'article Part-No. | DIN | øD1 mm | øD2 mm | L mm | L1 mm | A mm | S mm | Werkzeuge Outils Toolings |
|-----------------|-------|---|-----|-----------|-----------|---------|----------|---------|---------|-------------------------------------|
| 0.25-0.5 | 24-22 | 3739 | 0.5 | 1 | 1.4 | 14 | 8 | 4 | 0.5 | 3975d |
| 0.5-1 | 22-18 | 3740 | * | 1.7 | 1.9 | 15 | 8 | 5 | 0.8 | 3975d, 3980n, 3983p.2, 3984e |
| | 22-18 | 3740l | 1 | 1.6 | 1.9 | 17 | 10 | 5 | 0.8 | |
| 1.5-2.5 | 16-14 | 3741 | 2.5 | 2.3 | 1.9 | 17 | 10 | 5 | 0.8 | |
| | 16-14 | 3741k | * | 2.3 | 1.9 | 12 | 5 | 5 | 0.8 | |
| | 16-14 | 3741l | * | 2.3 | 1.9 | 22 | 15 | 5 | 0.8 | |
| 4-6 | 12-10 | 3742 | 6 | 3.4 | 2.8 | 20 | 10 | 6 | 1 | 3980n, 3984f |



UL-No. E235797

| mm ² | AWG | Artikelnummer Numéro d'article Part-No. | DIN | øD1 mm | B mm | H mm | L mm | L1 mm | A mm | S mm | Werkzeuge Outils Toolings |
|-----------------|-----|---|-----|-----------|---------|---------|---------|----------|---------|---------|---------------------------------|
| 10 | 8 | 3743 | 10 | 4.5 | 4.3 | 2.4 | 22 | 12 | 8 | 1.1 | 3980p, 3981an, 3982cn |
| 16 | 6 | 3744 | 16 | 5.8 | 5.5 | 2.6 | 26 | 13 | 10 | 1.2 | |
| 25 | 4 | 37441 | * | 6.7 | 6.8 | 2.6 | 33.5 | 15 | 13.5 | 1.2 | 3981an, 3982cn, 3982g |
| 35 | 2 | 37442 | * | 8.9 | 8 | 3 | 39 | 20 | 14 | 1.4 | |
| 50 | 1/0 | 37443 | * | 9.8 | 9.5 | 3.6 | 45 | 20 | 19 | 1.8 | |
| 70 | 2/0 | 37444 | * | 11.2 | 11 | 4 | 55 | 23 | 24 | 2 | |