

Concentricity gauge

Application:

For measuring the axial and radial run-out precision of shafts.

Execution:

- 2 movable tailstocks and 1 measuring stand for holding a dial gauge or precision pointer
- 1 tailstock with fixed tip and 1 tailstock with movable tip, adjustable using hand lever (sleeve and centre point made from one piece)
- Evenness tolerance of measuring surfaces in line with DIN 876-2. Tailstocks with 75 mm tip height have vee block surfaces
- Location hole for a dial gauge or precision pointer 8 H 7

Art. no.	35480 005
Brand	HELIOS-PREISSER
Manufacturer Part Number	6060780101
Point height	50 mm
Max. point width	200 mm
Base plate length	350 mm
Base plate width	110 mm
Groove width	10 mm
Weight	8 kg
Gross Weight	10.235 kg
Product Group	308



EAN

4029713223465