

Cordless drill driver

M12BDD



Execution:

- Single-cell monitoring for a long battery service life
- Optimised handle with soft-grip support for outstanding ergonomics and grip
- 10 mm FIXTEC metal quick-action drill chuck with spindle lock function
- 19-step torque setting with additional drilling step
- LED light illuminates the work area
- Battery state-of-charge indicator

Advantage:

- REDLINK™ electronics - Overload protection for long battery, motor and gear life
- System fully compatible with the Milwaukee® M12 product range



Art. no.	70700 330
Brand	MILWAUKEE
Manufacturer Part Number	493344 1915
Model	M12BDD-202C
Number of rechargeable batteries/batteries	2 PCS
Battery designation	M12 B2
Rechargeable battery/battery capacity	2 Ah
Weight of rechargeable battery/battery	0.2 kg
Battery included	Yes
Type of rechargeable battery/battery	Li-Ion
Battery voltage	12 V/AC
Nominal energy	24 Wh
Manufacturer Article Number	493344 1915
Max. drilling diameter in steel	10 mm
Max. drilling diameter in wood	22 mm
Idle speed 1st gear min.	0 1/min
Idle speed 1st gear max.	450 1/min
Idle speed 1st gear min./max.	0-450 1/min
Idle speed 2nd gear min.	0 1/min
Idle speed 2nd gear max.	1500 1/min
Idle speed 2nd gear min./max.	0-1500 1/min
Max. torque	30 Nm
Weight	1.2 kg
Included in delivery	2 x 12 V/2 Ah Red Li-ion rechargeable battery, 10 mm FIXTEC metal quick-action drill chuck, charger C12 C, bit, transport case, rechargeable battery(ies): 2 x M12 B2
Gross Weight	3.340 kg
Product Group	7MA

EAN

4002395002627