



GE
Lighting



PAR 56
300PAR56/NSP 240V

18676

Product information

PAR lamps provide a robust and flexible design solution for a wide range of applications. Choice of PAR36, PAR46, PAR56 or PAR64

- 3000 K or 4200 K colour temperature
 - Choice of beam widths
 - Excellent colour rendering
 - High efficiency combined with low operating costs
 - Robust and reliable
 - UV control
 - Easy retrofit
 - Colour consistent throughout life
 - Colour blends with halogen and fluorescent
-



Product data

EAN Code	0043168186766
DUN Code	00043168186766
Bulb Shape	PAR
Bulb Finish	Aluminized
Bulb Diameter [mm]	177.8
Cap/Base	GX16d
Nominal beam angle [°]	19
Gross weight per piece [g]	694
Maximum Overall Length [mm]	127
Net weight per piece [g]	625
Brand	General Electric (GE)

Performance data

Nominal power [W]	300
Nominal lamp voltage [V]	245
Nominal lumens [lm]	3450
Nominal correlated colour temperature (CCT) [K]	2750
Rated Life [h]	2000
Ballast Required	No
Nominal center beam candlepower (CBCP) [cd]	40000
Coil type	CC-13
Energy efficiency class (EEC)	E
Weighted energy consumption [kWh/1000h]	285.58

Logistic data

Pack Quantity	12
Pallet quantity EUR (PC)	192
Pallet quantity UK (PC)	264
Outer case size	349 x 300 x 446 (mm)
Layer quantity	96 EUR, 132 UK
Layer quantity EUR	96
Layer quantity UK	132
Product status	Available

Application areas



Club and Disco

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Entertainment Solution Spectrum Catalogue \(PDF\)](#)

[Lighting design tools & calculators \(PDF\)](#)

Disclaimer

Special purpose lamp – Stage Studio. Not suitable for household illumination.