

## SPANNFIX STANDARD - PRODUCT RANGE

### 9-215 SPANNFIX

for fixed screwing on



#### DESCRIPTION

The Spanifix **9-215** is suitable for all workbenches and surfaces due to its screwable base. The vice can be fixed with four holes (Ø 9 mm) to each table top. Slight pressure on the lever is sufficient and the clamped work piece can be moved into any suitable position.

|                    |        |
|--------------------|--------|
| Clamping pressure: | 1470 N |
| Clamping capacity: | 70 mm  |
| Clamping depth:    | 38 mm  |
| Jaw width:         | 50 mm  |



Position as picture:  
approx. 220 x 160 x 115 mm  
(Dimensions for orientation)



Weight: 1310 g



### 9-205 ESD SPANNFIX

for screwing, with ESD coating and ESD clamping jaws



#### DESCRIPTION

The Spanifix **9-205 ESD** with dissipative powder coating is suitable for workbenches or work areas with a maximum table thickness of up to 80 mm. Due to its table clamping, the small vice with ball joint can be quickly and easily mounted to any workbench or table. Slight pressure on the lever is sufficient and the clamped work piece can be moved into any suitable position.

|                    |        |
|--------------------|--------|
| Clamping pressure: | 1470 N |
| Clamping capacity: | 70 mm  |
| Clamping depth:    | 38 mm  |
| Jaw width:         | 50 mm  |



Position as picture:  
approx. 310 x 160 x 75 mm  
(Dimensions for orientation)



Weight: 1430 g



SPANNFIX