


Cabinet workbench series V 1500 with lowerable transport wheels

Zinc sheet coating 1500 mm, 4 drawers with full extension, 1 door, lever-operated wheels



Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 4 drawers with 100% full extension on the left, 2 x front height 90 mm, 2 x front height 180 mm, 1 door, height 540 mm on the right



Art. no.	50221 535
Brand	ANKE
Working height	850 mm
Worktop width	1500 mm
Number of drawers	4 PCS
Worktop height	50 mm
Number of doors	1 PCS
Worktop depth	700 mm
Pullout type	Full extension
On castors	Yes
Colour of front	Anthracite grey RAL 7016
Cabinet colour	Light grey RAL 7035
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Surface	Powder-coated
Load-carrying capacity	450 kg
Levelling	Yes
Lock type	DOM® locking system
Material of worktop	Zinc sheet covering
Drawer front height	2 x 90 mm, 2 x 180 mm
Drawer width (inner dimension)	500 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Central locking	Yes
Gross Weight	167.414 kg
Product Group	502

EAN

4014641160609