

SAIEW-M12S-5S-TL-HW-PG9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Type	SAIEW-M12S-5S-TL-HW-PG9
Order No.	1467760000
Version	Built-in plugs, M12, No. of poles: 5
GTIN (EAN)	4050118273458
Qty.	15 pc(s).

SAIEW-M12S-5S-TL-HW-PG9**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 18.8 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Standards

Connector standard IEC 61076-2-101

General data

Coding	A	Conductor O.D.	-
Connection thread	M12	Contact surface	Gold-plated
Housing main material	Zinc diecast	No. of poles	5
Protection degree	IP67, when fully mounted	Rated current	4 A
Rated current	4 A (4- and 5-pole)/ 2 A (8-pole)/ 1.5 A (12-pole)	Rated voltage	125 V
Rated voltage (text)	250 V (4-pole)/ 60 V (5-pole)/ 30 V (8 and 12-pole)	Temperature range of housing	-20 ... +90 °C
Type of connection	Pin		

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC002638
eClass 6.2	27-26-07-02	eClass 7.1	27-44-01-02
eClass 8.1	27-44-01-02	eClass 9.0	27-44-03-09
eClass 9.1	27-44-03-09		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)

Engineering Data [STEP](#)

Data sheet

SAIEW-M12S-5S-TL-HW-PG9

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Pole scheme

