

NdFeB MAGNET

N35SH - cylindrical



MAGNET DATA

			Limits			
Parameter	Symbol	Note	Min.	Тур.	Max.	Unit
Material	NdFeB	N35SH				
Magnetic Flux Density	Br		11700		12100	G
Temp. Coefficient of Flux Density	α(Br)			-0.12		%/°C
Operating Temperature	ТА				150	°C
Number of Pole Pairs	Р	1				
Direction of Magnetization		see dwg.				
Mechanical Dimensions				10		
outer diameter	n OD		0.9 2.9	1.0 3.0	1.1 3.1	mm mm

Treatment of edges:	without ridge
Treatment of the surface:	none
Plating:	NiCuNi-coating
Marking:	none

CAUTION: NdFeB-magnets are sensitive against corrosion and hence are protected by means of a NiCuNi-layer that covers the whole magnet surface. Precautions have to be taken that the protection layer will not be damaged during handling and/or due to physical or chemical impact.

INDUCTION AS A FUNKTION OF AIRGAP (typ. values)

Airgap, d [mm]	0,5	1,0	1,5	2,0	3,0	4,0
Induction, B [Gauß]	-	617	383	224	120	56

Airgap d is defined as the distance between sensor surface and magnet surface. Induction B measured with a calibrated Hallsensor (UGN3503U/UA - CAL). The minimum 3sigma induction is approximately 10% lower than the typical value.

ORDER NUMBER: 009.0021