

1 Identification of the substance/mixture and of the company/undertaking

- **Product identifier**
- **Trade name:** *UHU Alleskleber*
- **Relevant identified uses of the substance or mixture and uses advised against**
- **Application of the substance / the preparation** *Adhesives*
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
*UHU GmbH & Co.KG
 Herrmannstraße 7
 D-77815 Bühl (Baden)
 Tel.: 0049-(0)7223-284-0
 email: info@uhu.boltongroup.de*
- Fax: 0049-(0)7223-284-245
- **Further information obtainable from:** *CRD*
- **Emergency telephone number:** *0049-(0)7223284-363/-370*

2 Hazards identification

- **Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC**



F; Highly flammable

R11: Highly flammable.

- **Information concerning particular hazards for human and environment:**

The product has to be labelled due to the calculation procedure of the "General Classification guideline for preparations of the EU" in the latest valid version.

- **Classification system:**

The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

- **Label elements**

- **Labelling according to EU guidelines:**

The product has been classified and marked in accordance with EU Directives / Ordinance on Hazardous Materials.

The R and S phrases may be omitted if packaging contains no more than 0.125 litre.

- **Code letter and hazard designation of product:**

F Highly flammable

- **Risk phrases:**

11 Highly flammable.

- **Safety phrases:**

7/9 Keep container tightly closed and in a well-ventilated place.

16 Keep away from sources of ignition - No smoking.

23 Do not breathe fumes/aerosol.

51 Use only in well-ventilated areas.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.02.2011

Revision: 02.02.2011

Trade name: UHU Alleskleber

(Contd. of page 1)

- **Special labelling of certain preparations:**
After article 10 no. 4 of DIRECTIVE 1999/45/EC it shall not be necessary to indicate the R phrases or the S phrases, if the contents of the package do not exceed 125 ml.
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization: Mixtures**
- **Description:** Adhesive

- **Dangerous components:**

CAS: 79-20-9 EINECS: 201-185-2	methyl acetate Xi R36; F R11 R66-67 Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	50-100%
CAS: 67-64-1 EINECS: 200-662-2	acetone Xi R36; F R11 R66-67 Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	5,0-<10%

- **Additional information:** For the wording of the listed risk phrases refer to section 16.

4 First aid measures

- **Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** Do not induce vomiting; call for medical help immediately.

5 Firefighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Ensure adequate ventilation
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Pick up mechanically.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.

(Contd. on page 3)

Trade name: UHU Alleskleber

See Section 13 for disposal information.

(Contd. of page 2)

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.

8 Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

67-64-1 acetone

IOELV ()	1210 mg/m ³ , 500 ppm
----------	----------------------------------

- **Additional information:** The lists valid during the making were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
Avoid direct contact with the chemical/ the product/ the preparation by organizational measures.
- **Respiratory protection:** Not required.
- **Protection of hands:**
Solvent resistant gloves
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Fluid
Colour:	Colourless
Odour:	Characteristic

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.02.2011

Revision: 02.02.2011

Trade name: UHU Alleskleber

(Contd. of page 3)

· Change in condition Melting point/Melting range: Undetermined. Boiling point/Boiling range: 55°C	
· Flash point:	-13°C
· Ignition temperature:	425°C
· Self-igniting:	Product is not selfigniting.
· Danger of explosion:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	3,1 Vol %
Upper:	16,0 Vol %
· Vapour pressure at 20°C:	220 hPa
· Density at 20°C:	0,99 g/cm ³
· Solubility in / Miscibility with water:	Partly miscible.
· Viscosity:	
Dynamic at 20°C:	4400 mPas
· Solvent content:	
Organic solvents:	65,8 %
Water:	0,4 %
VOC (EC)	65,85 %
· Solids content:	33,8 %

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**

· **LD/LC50 values relevant for classification:**

79-20-9 methyl acetate

Oral	LD50	3705 mg/kg (rabbit)
------	------	---------------------

64-17-5 ethanol

Oral	LD50	7060 mg/kg (rat)
------	------	------------------

Inhalative	LC50/4 h	20000 mg/l (rat)
------------	----------	------------------

67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
------	------	------------------

Dermal	LD50	20000 mg/kg (rabbit)
--------	------	----------------------

- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.

(Contd. on page 5)

Trade name: UHU Alleskleber

(Contd. of page 4)

· **Sensitization:** No sensitizing effects known.

12 Ecological information

- **Toxicity**
- **Acquatic toxicity:** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Do not allow product to reach ground water, water course or sewage system.
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Disposal must be made according to official regulations.

· **European waste catalogue**

08 04 09*	waste adhesives and sealants containing organic solvents or other dangerous substances
-----------	--

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

· **Land transport ADR/RID (cross-border)**



- **ADR/RID class:** 3 Flammable liquids.
- **Danger code (Kemler):** 33
- **UN-Number:** 1133
- **Packaging group:** III
- **Hazard label:** 3
- **UN proper shipping name:** 1133 KLEBSTOFFE, Sondervorschrift 640H
- **Limited quantities (LQ)** LQ7
- **Transport category** 3
- **Tunnel restriction code** D/E

· **Maritime transport IMDG:**



- **IMDG Class:** 3
- **UN Number:** 1133
- **Label** 3
- **Packaging group:** III

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.02.2011

Revision: 02.02.2011

Trade name: UHU Alleskleber

(Contd. of page 5)

- **EMS Number:** F-E,S-E
- **Marine pollutant:** No
- **Proper shipping name:** ADHESIVES

 · **Air transport ICAO-TI and IATA-DGR:**


- **ICAO/IATA Class:** 3
- **UN/ID Number:** 1133
- **Label:** 3
- **Packaging group:** III
- **Proper shipping name:** ADHESIVES

- **UN "Model Regulation":** UN1133, ADHESIVES, 3, III
- **Special precautions for user** Warning: Flammable liquids.

15 Regulatory information

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

R11 Highly flammable.

R36 Irritating to eyes.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.

- **Department issuing MSDS:** CRD

- **Contact:**

Frau A. Liar,

Herr Dr. C. Hanf

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)

ICAO: International Civil Aviation Organization

ICAO-TI: Technical Instructions by the "International Civil Aviation Organization" (ICAO)

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent