

M12 MALE 0° / M12 FEMALE 0°

PVC 3X0.34 YELLOW, UL/CSA 0.3m

Male straight to female straight

M12 - M12, 3-pole


Art.-No. 7005 - M12 Lite - (plastic hexagonal screw) on request

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.

[Link to Product](#)**Illustration**

Male

Female





Product may differ from Image

Approvals



* only for products with UL/CSA approved cable

Form

40001

Technical Data

| | |
|------------------------------------|---|
| Operating voltage | max. 250 V AC/DC |
| Operating voltage (only UL listed) | * 30 V DC |
| Operating current per contact | max. 4 A |
| Contact resistance | max. 5 mW |
| Isolation resistance | 100000 MW |
| Locking of ports | Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing |
| Protection | IP67 inserted and tightened (EN 60529) |

Cables

| | |
|-----------------------------|--------------------------------|
| Cable number | 013 |
| No./diameter of wires | 3 × 0.34 mm ² |
| Wire isolation | PVC (br, bl, bk) |
| Jacket Color | yellow |
| Shore hardness outer jacket | 85 ± 5A |
| Material (jacket) | PVC (UL/CSA) |
| Material (wire) | Cu (blanc), Class 5 (IEC60228) |
| Outer diameter | approx. 4.6 mm |
| Bend radius (fixed) | 5 × outer Ø |

The information in this brochure has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

| | |
|----------------------------|--------------|
| Bend radius (moving) | 10 × outer Ø |
| Temperature range (fixed) | -30...+80 °C |
| Temperature range (mobile) | -5...+80 °C |

General data

| | |
|-------------------|--|
| Temperature range | -25...+85 °C, depending on cable quality |
| Pollution Degree | 3 |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85444290 |
| minimum order quantity | 1 |