


SA5014

Flow sensor

SAD10XDB50KG/US-100



- 1 LEDs Display unit
- I, II not used
- 2 alphanumeric display 4-digit red/green
- 3 programming buttons
- 4 upper part of the housing can be rotated 345°



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 2	
Process connection	threaded connection M18 x 1,5 internal thread	
Liquids		
Measuring range	[ft/s]	0.15...9.85
Gases		
Measuring range	[ft/s]	6...328

Application

Special feature	Gold-plated contacts	
Media	water; glycol solutions; air; oils	
Note on media	low-viscosity oils with viscosity: ≤ 40 mm²/s (104 °F)	high-viscosity oils with viscosity: > 40 mm²/s (104 °F)
Medium temperature	[°F]	-4...194
Pressure rating	[bar]	100

Flow sensor

SAD10XDB50KG/US-100

Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 100
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	10
Inputs / outputs		
Number of inputs and outputs		Number of analogue outputs: 2
Outputs		
Total number of outputs		2
Output signal		analogue signal
Number of analogue outputs		2
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	350
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	45
Operating mode		relative; absolutely liquid; absolutely gaseous
Note on setting range		Operating mode: relative
Liquids		
Measuring range	[ft/s]	0.15...9.85
Resolution	[ft/s]	0.05
Setting range	[ft/s]	0...19.5
Analogue start point ASP	[ft/s]	0...7.95
Analogue end point AEP	[ft/s]	1.9...9.85
Gases		
Measuring range	[ft/s]	6...328
Resolution	[ft/s]	2
Setting range	[ft/s]	0...656
Analogue start point ASP	[ft/s]	0...264
Analogue end point AEP	[ft/s]	64...328
Temperature monitoring		
Measuring range	[°F]	-4...194
Resolution	[°F]	0.5
Analogue start point	[°F]	-4...169
Analogue end point	[°F]	39...212
In steps of	[°F]	0.5

SA5014



Flow sensor

SAD10XDB50KG/US-100

Accuracy / deviations

Flow monitoring

Temperature drift [cm/s x 1/K]	0,01 fps x 1/K (< 68 °F; > 158 °F)
Temperature gradient [K/min]	100
Accuracy	± (7 % MW + 2 % MEW); (Für Relativmodus im Bereich der größten Empfindlichkeit mit; water: 68...158 °F; inlet length: 5 ft; DN25 (DIN 2448); mounting position according to instructions; Accuracy can differ for other media and mounting positions.)
Repeatability	0,05 m/s; (water; flow velocity: 0,05...3 m/s)

Temperature monitoring

Temperature drift	± 0,003 K/°F
Accuracy [K]	± 0,3 / ± 1; (water; flow velocity: 1...9,85 fps / air; flow velocity: > 32,8 fps)

Response times

Flow monitoring

Response time [s]	0.5; (T09; water; glycol: 0,8 s; air: 7 s; oil: 1,8 s; each T09)
Temperature monitoring	

Dynamic response T05 / T09 [s]

1,5 (T09); (water; flow velocity: 0,3...3 m/s)

Software / programming

Parameter setting options	medium selection; Damping; Teach function; display can be rotated and switched off; standard unit of measurement; process value colour
---------------------------	--

Operating conditions

Ambient temperature [°F]	-40...176
Storage temperature [°F]	-40...212
Protection	IP 65; IP 67

Tests / approvals

EMC	DIN EN 60947-5-9
Shock resistance	DIN EN 60068-2-27
Vibration resistance	DIN EN 60068-2-6
MTTF [years]	179
UL approval	UL Approval no. I004 File number UL E174189

Mechanical data

Weight [g]	278
Materials	stainless steel (1.4404 / 316L); stainless steel (1.4310 / 301); PBT-GF20; PBT-GF30
Materials (wetted parts)	stainless steel (1.4404 / 316L); Gasket: FKM
Process connection	threaded connection M18 x 1,5 internal thread

Displays / operating elements

Display	Display unit measured values	6 x LED, green (%), m/s, l/min, m³/h, °C, 10³) alphanumeric display, red/green 4-digit
---------	---------------------------------	---

Remarks

Remarks	MW = measured value MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection


Connector: 1 x M12; Contacts: gold-plated

SA5014




Flow sensor

SAD10XDB50KG/US-100



Connection



colours to DIN EN 60947-5-2

OUT1: analogue output Temperature monitoring

OUT2: analogue output volumetric flow quantity monitoring

Core colours :

BK = black

BN = brown

BU = blue

WH = white