


High-Temperature Resistant Actuator and Sensor Cable Extension Cable
HT-SKP4-5-HT-SSP4/S2430



- M8 female connector, straight, 4-pin
- M8 male connector, straight, 4-pin
- Sheath material: PTFE
- Sheath color: white
- Flame-retardant
- Resistant to welding sparks
- Resistant to chemicals, UV radiation and oils
- Resistant to acids and alkaline solutions
- LABS free
- Resistant to microbes and hydrolysis
- Cold and heat-flexible
- RoHS-compliant
- Protection class IP65
- Temperature range of the cable: -190°C...260°C
- Cable length: 5.0 m

Type designation	HT-SKP4-5-HT-SSP4/S2430
Ident no.	8039976

Connector A side	Female connector, M8 (← 1, Straight
Number of pins	4
Contacts	Brass, CuZn, Gold-plated
Contact carriers	Plastic, PBT GF, Black
Grip	Plastic, PBT GF, Black
Coupling nut/screw	Brass, CuZn, Nickel-plated
Seal	Plastic, FPM/FKM
Protection class	IP65, A + B side screwed together
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Tightening torque	0.5 ... 0.6 Nm (observe max. torque of counter piece!)



Connector B side	Connector, M8x1, Straight
Number of pins	4 pins
Contacts	brass, CuZn, Gold-plated
Contact carriers	Plastic, PBT GF, Black
Grip	plastic, PBT GF, black
Coupling nut/screw	Brass, CuZn, Nickel-plated
Protection class	IP65, Only when screwed tight
Mechanical lifespan	> 100 Mating cycles
Pollution degree	3
Tightening torque	0.5 ... 0.6 Nm (observe max. torque of counter piece!)

General data	
Cable diameter	3.8 ± 0.20mm
Cable length	5 m
Cable quality	PTFE
Cable color	White
Core insulation	PTFE
Core colors	BN, WH, BU, BK
Core cross-section	4x0.34mm ²
Arrangement of strands	7x0.254 mm

Electrical features at +20 °C	
Current	4 A
Rated voltage	250 V
Forward resistance	≤ 5 mΩ

Mechanical and chemical properties	
Bending radius (stationary laying)	> 5 x Ø
Bending radius (flexible use)	> 10 x Ø
Ambient temperature	
Stationary	-20...+150°C

Cable Cross-section



Circuit Diagram

