


## +8dBi Fibreglass Rod

- 4G GSM Omni Directional Antenna
- 806-960 / 1710-2700MHz
- World-Wide Use
- DIA 60 x 750mm
- 6-8dBi Gain
- Vertical Polarisation
- VSWR <1.5
- 30cm SMA Type Connector
- 5m RG174 Coax to SMA (M) Bundled
- Max 100W Power
- Operates -40 to +60degC
- Weight 1.5Kg

### Applications

- GSM / LTE Applications
- Machine to Machine
- Industrial Systems



### Description

A Rugged Fibre-Glass Rod Omni-Directional antenna with high performance Gain for worldwide use. Supplied with Wall mounting Brackets, the antenna has a 30cm Cable with SMA(m) Type fixing and is supplied with a 5 metre Coax Cable with SMA male connector

Part No	Description	Connector
ANT-GROD8-NSMA	Rod Antenna	SMA (M)

# ANT-GROD8

---



## **RF Solutions Ltd. Recycling Notice Meets the following EC Directives:**

### **DO NOT**

Discard with normal waste, please recycle.

### **ROHS Directive 2002/95/EC**

Specifies certain limits for hazardous substances.

### **WEEE Directive 2002/96/EC**

Waste electrical & electronic equipment. This product must be disposed of through a licensed WEEE collection point. RF Solutions Ltd., fulfills its WEEE obligations by membership of an approved compliance scheme.

[www.rfsolutions.co.uk](http://www.rfsolutions.co.uk)

**RF Solutions Ltd**

William Alexander House, William Way, Burgess Hill, West Sussex, RH15 9AG  
Sales: +44(0)1444 227 910      Tech Support: +44(0)1444 227909

